


RED INDICATES ORIGINAL

DASH NO	DESCRIPTION
-1	TERM (NO CHAIN)
-2	TERM WITH 2.50 BRASS CHAIN
-3	TERM WITH 2.50 NYLON CHAIN
-4	TERM WITH 3.00 BRASS CHAIN
-5	TERM WITH 3.00 NYLON CHAIN
-6	TERM WITH 6.00 BRASS CHAIN
-7	TERM WITH 6.00 NYLON CHAIN
-8	TERM WITH 4.00 BRASS CHAIN
-9	TERM WITH 4.00 NYLON CHAIN
-10	TERM WITH 10.00 BRASS CHAIN
-11	TERM WITH 10.00 NYLON CHAIN
-12	TERM WITH 2.50 JACKETED SST ROPE
-13	TERM WITH 3.00 JACKETED SST ROPE
-14	TERM WITH 6.00 JACKETED SST ROPE
-15	TERM WITH 4.00 JACKETED SST ROPE
-16	TERM WITH 7.00 JACKETED SST ROPE
-17	TERM WITH 4.50 JACKETED SST ROPE

DASH	"A" DIA	"B" DIA	"C" DIM	"D" DIM
-01	.755	.875	1.191	.513
-02	.630	.750	1.066	.450
-03	.505	.625	.941	.388
-04	.439	.562	.878	.356
-05	.380	.500	.816	.325
-06	.317	.437	.753	.294
-07	.281	.406	.722	.278
-08	.610	.750	1.066	.450
-09	.567	.687	1.003	.419
-010	.192	.312	.628	.231
-011	1.005	1.125	1.441	.638
-008	.330	.450	.765	.300

INCH	MM	INCH	MM	INCH	MM	INCH	MM	INCH	MM
.005	0.13	.290	7.37	.439	11.15	.639	16.21	1.086	27.06
.010	0.25	.294	7.47	.450	11.43	.687	17.45	1.125	28.58
.029	0.74	.300	7.62	.500	12.70	.722	18.34	1.191	30.20
.030	0.76	.312	7.92	.505	12.83	.750	19.05	1.240	31.50
.032	0.81	.317	8.05	.513	13.03	.753	19.13	1.705	43.31
.062	1.57	.325	8.26	.516	14.22	.755	19.18	2.50	63.50
.140	3.56	.330	8.38	.562	14.27	.766	19.46	3.00	76.20
.192	4.88	.356	9.04	.587	14.40	.816	20.73	4.00	101.60
.230	5.08	.380	9.65	.594	15.05	.875	22.23	4.50	114.30
.200	5.09	.389	9.86	.610	15.49	.878	22.30	6.00	152.40
.25	6.35	.406	10.31	.625	15.89	.941	23.90	7.00	177.80
.278	7.06	.419	10.64	.628	15.95	1.005	25.48	10.00	254.00
.281	7.14	.437	11.00	.630	16.00	1.005	25.53		

DATA CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO THOMPSON ELECTRONICS INC. AND SHALL NOT BE DISCLOSED, COPIED OR USED FOR PROCUREMENT OR MANUFACTURE WITHOUT EXPRESS WRITTEN PERMISSION.		REVISONS		310-0049	SH IC
REV	EO	DESCRIPTION		DWN	APPROVED
G	13251	UPDATED TABLE 2; SEE ECO		DKC	5/17/00



NOTE THAT CHAIN LENGTH FOR SST ROPE WITH MOUNTING
OPTION IS NOT MEASURED TO CENTER OF BULKHEAD
MOUNTING LUG

5. EXAMPLE OF COMPLETE MODEL NO:

BASIC MODEL NO:
TNT1 = W/O SAFETY WIRE HOLE
TNTS1 = W/SAFETY WIRE HOLES

TNT1 -2 -3 -02

BULKHEAD JACK MOUNTING LUG (OPTIONAL) AVAILABLE WITH BRASS, OR NYLON CHAIN, & SST ROPE (SEE TABLES 1, & 2)



DASH NO. FOR CHAIN/ROPE MATL. & LENGTH (SEE TABLE 1)

4. CONCENTRIC TWINAX/TRIAX THREADED TERMINATION PLUG

3 RESISTANCE VALUE IN OHMS (1/2W, 1%)
S = CENTER CONTACT SHORTED TO INTERMEDIATE CONTACT
(NO RESISTOR)
O = NO RESISTOR, CONTACT NOT SHORTED, AND CONNECTOR IS SUPPLIED
LOOSELY ASSEMBLED (CUSTOMER TO COMPLETE THE ASSEMBLY) NOTE:
FOR SPECIAL RESISTOR VALUES, SEE DWG 315-0037

2. FINISH: TFS-1A (NICKEL)

1. ALL DIM ARE IN INCHES



QTY		DESCRIPTION		PART NUMBER	ITEM
TOL. UNLESS SPECIFIED		TROMPETER ELECTRONICS, INC.		TNT1/TNTS1	
.10X .005					
.000X .005					
.000X .005					
ANGLSTZ		MATERIAL	CODE IDENT	DRAWING NO.	REV
DWN DKL 2-7-00		14949		310-0049	G
CHK 5/12/02					
ENGR					
NEXT ASSY	APPR 5/12/02	SCALE 4/1	DATE 9/4/00	SHEET 1C	