


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



| PANDUIT<br>PART NO. | BUNDLE DIA.     |                 | A<br>in<br>(mm) | B<br>in<br>(mm) | C<br>in<br>(mm) | D<br>in<br>(mm) | E<br>in<br>(mm) | F<br>in<br>(mm) | MIN. LOOP<br>TENSILE<br>lbs. (N) | CROSS<br>SECTION | WEIGHT<br>100 pcs<br>lbs (g) |
|---------------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|----------------------------------|------------------|------------------------------|
|                     | MIN. in<br>(mm) | MAX. in<br>(mm) |                 |                 |                 |                 |                 |                 |                                  |                  |                              |
| SG200S              | .06<br>(1.5)    | 2.0<br>(51)     | .046<br>(1.2)   | .225<br>(5.7)   | .290<br>(7.4)   | .220<br>(5.6)   | .342<br>(8.7)   | 8.3<br>(210.8)  | 50 (222)                         | STANDARD         | .30<br>(137)                 |
| SG250S              | .16<br>(4.1)    | 2.6<br>(66)     | .050<br>(1.3)   | .225<br>(5.7)   | .318<br>(8.1)   | .220<br>(5.6)   | .360<br>(9.1)   | 10.4<br>(264.2) | 75 (334)                         | STANDARD         | .41<br>(186)                 |
| SG300S              | .16<br>(4.1)    | 3.2<br>(81)     | .050<br>(1.3)   | .225<br>(5.7)   | .318<br>(8.1)   | .220<br>(5.6)   | .360<br>(9.1)   | 12.4<br>(315.0) | 75 (334)                         | STANDARD         | .49<br>(220)                 |
| SG370S              | .16<br>(4.1)    | 4.2<br>(107)    | .052<br>(1.3)   | .225<br>(5.7)   | .330<br>(8.4)   | .220<br>(5.6)   | .360<br>(9.1)   | 15.3<br>(388.6) | 75 (334)                         | STANDARD         | .61<br>(278)                 |

**NOTE:**

1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE & PART COLOR.

|     |         |      |     |                                                       |  |       |   |      |     | DIMENSIONS IN PARENTHESIS ARE IN METRIC UNITS                                                                       |  |
|-----|---------|------|-----|-------------------------------------------------------|--|-------|---|------|-----|---------------------------------------------------------------------------------------------------------------------|--|
|     |         |      |     |                                                       |  |       |   |      |     | PANDUIT CORP. TINLEY PARK, ILLINOIS                                                                                 |  |
|     |         |      |     |                                                       |  |       |   |      |     | SUPER-GRIP CABLE TIES                                                                                               |  |
|     |         |      |     |                                                       |  |       |   |      |     | UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE:<br>(.X) ± (.XXX) ± .020 (.5)<br>(.XX) ±.02 (.5) ANGLES ± |  |
|     |         |      |     |                                                       |  |       |   |      |     | UNLESS OTHERWISE SPECIFIED,<br>ALL DIMENSIONS ARE GIVEN<br>IN INCHES, THIRD ANGLE PROJECTION.                       |  |
|     |         |      |     |                                                       |  |       |   |      |     | DRAWN BY JABO MAT'L:                                                                                                |  |
|     |         |      |     |                                                       |  |       |   |      |     | SCALE NONE                                                                                                          |  |
| 2   | 9/19/07 | JABO |     | SG250S, SG300S, SG370S TENSILE WAS 70,<br>NOW 75 LBS. |  | 27441 | 2 |      |     | DATE 4/28/05                                                                                                        |  |
|     |         |      |     |                                                       |  |       |   |      |     | NYLON 6.6                                                                                                           |  |
| REV | DATE    | BY   | CHK | DESCRIPTION                                           |  | ECN   | R | CUST | SUP | DRAWING NO. SS-27441<br>SHEET 2 OF 3                                                                                |  |
|     |         |      |     |                                                       |  |       |   |      |     | DWG A<br>SIZE                                                                                                       |  |