





H
G
F
E
D
C
B
A

12 11 10 9 8 7 6 5 4 3 2 1

SYMBOL DEFINITION			MISSING NUMBERS
THE NUMBER INSIDE THE SYMBOL  CORRESPONDS TO THE NUMBER ON THE INSPECTION REPORT FOR THIS DRAWING/PART NUMBER	TOTAL NO. OF SYMBOLS ON DRAWING	6	
	LAST NO. USED	13	

DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	CK	APVD
DATE	STG	REV	CHG	N/P						
04N098	R	001	-	-		ALL PARTS - REDRAWN TO PD; 12047948 REVISED	188898	GEG	GMC	JR
04N098	R	002	-	-		ALL PARTS - UPDATED PDM ATTRIBUTES	191525	GEG	GMC	JR
04SE00	R	003	-	-		12186478 - MATL' SPEC WAS R0063785	202903	JYD	GMC	DN





NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION. (SEE MATH MODEL FOR PRECISE DIMENSIONS.) FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATING COMPONENTS OR EQUIVALENT: CONNECTOR 12047947

12186478	R	002	-		R0071769 PA66 HS IM GRA-LT	1.228
12047948	R	F	-		R0071754 PA66 HS IM-BLK	1.228
PART NO	STG	REV	N/P	STATUS	MATERIAL SPECIFICATION AND COLOR	VOL CM ³

(9-12) PROCESS SENSITIVE DIMENSION
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED

DELPHI Automotive Systems																																	
MATERIAL SPEC SEE CHART		<table><tr><th colspan="5">DIMENSIONAL RANGE (MM) CHART E</th></tr><tr><th>FROM</th><th>0</th><th>> 20</th><th>> 30</th><th>> 70</th></tr><tr><th>TO</th><th>20</th><th>30</th><th>70</th><th>100</th></tr><tr><td colspan="5">TOLERANCE UNLESS OTHERWISE SPECIFIED</td></tr><tr><td></td><td>±0.15</td><td>±0.2</td><td>±0.3</td><td>±0.4</td></tr><tr><td colspan="5">ANGULAR TOLERANCE ± 2°</td></tr></table>		DIMENSIONAL RANGE (MM) CHART E					FROM	0	> 20	> 30	> 70	TO	20	30	70	100	TOLERANCE UNLESS OTHERWISE SPECIFIED						±0.15	±0.2	±0.3	±0.4	ANGULAR TOLERANCE ± 2°				
DIMENSIONAL RANGE (MM) CHART E																																	
FROM	0	> 20	> 30	> 70																													
TO	20	30	70	100																													
TOLERANCE UNLESS OTHERWISE SPECIFIED																																	
	±0.15	±0.2	±0.3	±0.4																													
ANGULAR TOLERANCE ± 2°																																	
PART DRAWING																																	
CODE NUMBER 6900	DWG DATE 24FE96	SCALE 5:1																															
QC SPEC	STYLE	VOLUME cm ³ SEE DWG																															
PART GEOMETRY 3D SOLID	UNLESS OTHERWISE SPECIFIED: PERFECT FORM REQUIRED FOR FEATURES OF SIZE AT MMC. TRUE POSITION TOLERANCES AND RELATED DATUMS APPLY AT CONDITION OF SIZE INDICATED IN FEATURE CONTROL FRAME. ALL OTHER GEOMETRIC TOLERANCES AND RELATED DATUMS APPLY RFS. SEPARATE TRUE POSITION CALLOUTS MAY BE GAGED SEPARATELY, REGARDLESS OF DATUM REFERENCE.																																
 CHANGE RESTRICTED NO MANUAL CHANGES	REFERENCE 001,701																																
	DATE																																
COPY OF MATH DATA DO NOT SCALE	APVD1 G. ESTRADA 04N098																																
METRIC UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE IN MILLIMETERS	APVD2 G.MACIAS 10N098																																
	APVD3 J. REIDER 15MR99																																
	APVD4																																
	APVD5																																
THIRD ANGLE PROJECTION 	DRAWING NAME TAXI TPA M/P 150																																
SHEET NUMBER 1 OF 1	DRAWING NUMBER 12186580		DWG STATUS STG REV N/P R 003 -																														
			SIZE A1																														

H
G
F
E
D
C
B
A

12 11 10 9 8 7 6 5 4 3 2 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Delphi Connection Systems:](#)

[12047948](#)