




REV. 0
DCO 142821


COIL: @ 25°C
RESISTANCE 880 OHMS $\pm$ 10%
NOMINAL VOLTAGE 18.0 VDC
MUST OPERATE 10.6 VDC
MUST RELEASE 6.0 VDC MAX, 0.91 VDC MIN

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's
SHOCK 75 g's 6 MS. DURATION
TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2.0 MS MAX.
RELEASE TIME 4.0 MS MAX.
CONTACT BOUNCE 1.5 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. PBB 3/15/01

CK. EBY 3/15/01

CH Technologies
advanced control electronic solutions

CUST. QPL
CUST. NO. M39016/15-092L REV.

"JMAD" RELAY

JMACDG-18XL