

# Silicon NPN Planar RF Transistor

Electrostatic sensitive device.  
Observe precautions for handling.





## Applications



For low noise and high gain broadband amplifiers at collector currents from 1 mA to 20 mA.

## Features

- Low power applications
- Low noise figure
- High transition frequency



13 653



13 566

BFP182TW Marking: W82



Plastic case (SOT 343)

1 = Collector, 2 = Emitter, 3 = Base, 4 = Emitter

BFP182TRW Marking: WSG

Plastic case (SOT 343R)

1 = Collector, 2 = Emitter, 3 = Base, 4 = Emitter



94 9279

13 579

BFP182T Marking: 82P

Plastic case (SOT 143)

1 = Collector, 2 = Emitter, 3 = Base, 4 = Emitter

**Absolute Maximum Ratings** $T_{amb} = 25^\circ C$ , unless otherwise specified

Parameter	Test Conditions	Symbol	Value	Unit
Collector-base voltage		$V_{CBO}$	15	V
Collector-emitter voltage		$V_{CEO}$	10	V
Emitter-base voltage		$V_{EBO}$	2	V
Collector current		$I_C$	35	mA
Total power dissipation	$T_{amb} \leq 60^\circ C$	$P_{tot}$	200	mW
Junction temperature		$T_j$	150	$^\circ C$
Storage temperature range		$T_{stg}$	-65 to +150	$^\circ C$

**Maximum Thermal Resistance** $T_{amb} = 25^\circ C$ , unless otherwise specified

Parameter	Test Conditions	Symbol	Value	Unit
Junction ambient	on glass fibre printed board (25 x 20 x 1.5) mm <sup>3</sup> plated with 35 $\mu$ m Cu	$R_{thJA}$	450	K/W

## Electrical DC Characteristics



$T_{amb} = 25^\circ C$ , unless otherwise specified

Parameter	Test Conditions	Symbol	Min	Typ	Max	Unit
Collector cut-off current	$V_{CE} = 15 V, V_{BE} = 0$	$I_{CES}$			100	$\mu A$
Collector-base cut-off current	$V_{CB} = 10 V, I_E = 0$	$I_{CBO}$			100	nA
Emitter-base cut-off current	$V_{EB} = 1 V, I_C = 0$	$I_{EBO}$			1	$\mu A$
Collector-emitter breakdown voltage	$I_C = 1 mA, I_B = 0$	$V_{(BR)CEO}$	10			V
Collector-emitter saturation voltage	$I_C = 15 mA, I_B = 1.5 mA$	$V_{CEsat}$		0.1	0.4	V
DC forward current transfer ratio	$V_{CE} = 6 V, I_C = 5 mA$	$h_{FE}$	50	90	150	
	$V_{CE} = 8 V, I_C = 20 mA$	$h_{FE}$		100		

## Electrical AC Characteristics



$T_{amb} = 25^\circ C$ , unless otherwise specified

Parameter	Test Conditions	Symbol	Min	Typ	Max	Unit
Transition frequency	$V_{CE} = 6 V, I_C = 5 mA, f = 500 MHz$	$f_T$		5.5		GHz
	$V_{CE} = 8 V, I_C = 20 mA, f = 500 MHz$	$f_T$		7.5		GHz
Collector-base capacitance	$V_{CB} = 10 V, f = 1 MHz$	$C_{cb}$		0.3		pF
Collector-emitter capacitance	$V_{CE} = 8 V, f = 1 MHz$	$C_{ce}$		0.2		pF
Emitter-base capacitance	$V_{EB} = 0.5 V, f = 1 MHz$	$C_{eb}$		0.7		pF
Noise figure	$V_{CE} = 6 V, I_C = 5 mA, Z_S = Z_{Sopt}, f = 900 MHz$	$F$		1.5		dB
	$V_{CE} = 6 V, I_C = 5 mA, Z_S = Z_{Sopt}, f = 1.75 GHz$	$F$		2.0		dB
Power gain	$V_{CE} = 8 V, I_C = 20 mA, Z_S = 50 \Omega, Z_L = Z_{Lopt}, f = 900 MHz$	$G_{pe}$		18		dB
	$V_{CE} = 8 V, I_C = 20 mA, Z_S = 50 \Omega, Z_L = Z_{Lopt}, f = 1.75 GHz$	$G_{pe}$		12		dB
Transducer gain	$V_{CE} = 8 V, I_C = 20 mA, Z_0 = 50 \Omega, f = 900 MHz$	$ S_{21e} ^2$		15		dB

**Dimensions of BFP182TW in mm**


technical drawings  
according to DIN  
specifications

96 12237

**Dimensions of BFP182TRW in mm**

technical drawings  
according to DIN  
specifications

96 12238

**Dimensions of BFP182T in mm**


96 12240


 technical drawings  
according to DIN  
specifications

## Ozone Depleting Substances Policy Statement

It is the policy of **Vishay Semiconductor GmbH** to

1. Meet all present and future national and international statutory requirements.
2. Regularly and continuously improve the performance of our products, processes, distribution and operating systems with respect to their impact on the health and safety of our employees and the public, as well as their impact on the environment.

It is particular concern to control or eliminate releases of those substances into the atmosphere which are known as ozone depleting substances (ODSs).

The Montreal Protocol (1987) and its London Amendments (1990) intend to severely restrict the use of ODSs and forbid their use within the next ten years. Various national and international initiatives are pressing for an earlier ban on these substances.

**Vishay Semiconductor GmbH** has been able to use its policy of continuous improvements to eliminate the use of ODSs listed in the following documents.

1. Annex A, B and list of transitional substances of the Montreal Protocol and the London Amendments respectively
2. Class I and II ozone depleting substances in the Clean Air Act Amendments of 1990 by the Environmental Protection Agency (EPA) in the USA
3. Council Decision 88/540/EEC and 91/690/EEC Annex A, B and C (transitional substances) respectively.

**Vishay Semiconductor GmbH** can certify that our semiconductors are not manufactured with ozone depleting substances and do not contain such substances.

**We reserve the right to make changes to improve technical design and may do so without further notice.**

Parameters can vary in different applications. All operating parameters must be validated for each customer application by the customer. Should the buyer use Vishay-Telefunken products for any unintended or unauthorized application, the buyer shall indemnify Vishay-Telefunken against all claims, costs, damages, and expenses, arising out of, directly or indirectly, any claim of personal damage, injury or death associated with such unintended or unauthorized use.

Vishay Semiconductor GmbH, P.O.B. 3535, D-74025 Heilbronn, Germany  
Telephone: 49 (0)7131 67 2831, Fax number: 49 (0)7131 67 2423