



Model 3840 Adapter, BNC (Male), Resistor Termination**Features:**

- Reliable termination at known resistance value $\pm 1\%$
- Gold plated contacts for high conductance
- Tarnish resistant plating on body

Materials:

Body: Brass, Center Contact: Gold plated brass

Outer Contact: Tarnish Resistant gold plated Beryllium Copper.

Dielectric: Teflon

Gasket/Seals: Silicone rubber

Resistor: Deposited carbon film

Marking: "Pomona 3840"

Label: "TERM, * Ω 1/2W"

Ratings:

Frequency Range: DC to 500 MHz

Resistance Tolerance: $\pm 1\%$

Power: 1/2W @ 70°C Max

ORDERING INFORMATION: Model 3840-*

*= Resistance Value 50, 75, 93, 100, 600

Ordering Example: 3840-50 = 50 Ohms

Sales:
800-490-2361
Fax:
888-403-3360

Technical Support:
800-241-2060
or e-mail us at
technicalsupport@pomonatest.com

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.

Where to Buy: www.pomonaelectronics.com

Document Number Page 1 of 1