



## G4010 series



0.41 ± 0.02  
(10.3 ± 0.5)



AIR FLOW  
→



**(40 x 40 x 10.3 mm)**

1.57 x 1.57 x 0.41 inches

Construction: UL94V-0 PBT impeller & frame

Bearing option: ball bearing

Connection: AWG 26, UL1061 lead wires

Frame: ribbed

Protection: thermal

Options: tachometer output or locked rotor alarm signal

| Model No.     | Rated Voltage<br>V | Current mA |     |     | Speed<br>RPM | Air Volume |       | Max. Static Pressure (H <sub>2</sub> O) |      | Sound Noise<br>dB(A) | Weight<br>g |
|---------------|--------------------|------------|-----|-----|--------------|------------|-------|-----------------------------------------|------|----------------------|-------------|
|               |                    | 5          | 12  | 24  |              | M³/Min.    | CFM   | MM                                      | INCH |                      |             |
| <b>G4010S</b> | 5/12               | 90         | 60  | -   | 4,000        | 0.13       | 5.00  | 1.70                                    | 0.07 | 21                   | 12          |
| <b>G4010L</b> | 5/12/24            | 140        | 100 | 70  | 5,000        | 0.16       | 6.00  | 2.70                                    | 0.11 | 22                   | 12          |
| <b>G4010M</b> | 5/12/24            | 240        | 150 | 100 | 6,000        | 0.19       | 7.00  | 3.70                                    | 0.15 | 28                   | 12          |
| <b>G4010H</b> | 5/12/24            | 400        | 220 | 160 | 8,000        | 0.25       | 9.00  | 6.40                                    | 0.25 | 35                   | 12          |
| <b>G4010E</b> | 12/24              | -          | 350 | 250 | 10,000       | 0.32       | 11.00 | 9.90                                    | 0.39 | 41                   | 12          |