



# SPECIFICATION

- Supplier : Samsung electro-mechanics
- Product : Multi-layer Ceramic Capacitor

- Samsung P/N : [CL10F104ZO8NNND](#)
- Description : CAP, 100nF, -20/+80%, 16V, Y5V, 0603

## A. Samsung Part Number

**CL 10 F 104 Z O 8 N N N D**  
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

① <b>Series</b>	Samsung Multi-layer Ceramic Capacitor		
② <b>Size</b>	0603 (inch code)	L: $1.6 \pm 0.1$ mm	W: $0.8 \pm 0.1$ mm
③ <b>Dielectric</b>	Y5V	⑧ <b>Inner electrode</b>	Ni
④ <b>Capacitance</b>	100 nF	⑨ <b>Termination</b>	Cu
⑤ <b>Capacitance tolerance</b>	-20/+80 %	⑩ <b>Plating</b>	Sn 100% (Pb Free)
⑥ <b>Rated Voltage</b>	16 V	⑪ <b>Product</b>	Normal
⑦ <b>Thickness</b>	$0.8 \pm 0.1$ mm	⑫ <b>Special</b>	Reserved for future use
		⑬ <b>Packaging</b>	Cardboard Type, 13" reel

## B. Samsung Reliability Test and Judgement condition

	Performance	Test condition
<b>Capacitance</b>	Within specified tolerance	$1\text{kHz} \pm 10\%$ $1.0 \pm 0.2\text{Vrms}$
<b>Tan δ (DF)</b>	0.07 max.	
<b>Insulation Resistance</b>	10,000Mohm or $100\text{Mohm} \cdot \mu\text{F}$ Whichever is Smaller	Rated Voltage $60 \sim 120$ sec.
<b>Appearance</b>	No abnormal exterior appearance	Microscope ( $\times 10$ )
<b>Withstanding Voltage</b>	No dielectric breakdown or mechanical breakdown	250% of the rated voltage
<b>Temperature Characterisitcs</b>	Y5V (From $-30^\circ\text{C}$ to $85^\circ\text{C}$ , Capacitance change shoud be within $-82\sim+22\%$ )	
<b>Adhesive Strength of Termination</b>	No peeling shall be occur on the terminal electrode	$500\text{g}\cdot\text{F}$ , for $10 \pm 1$ sec.
<b>Bending Strength</b>	Capacitance change : within $\pm 30\%$	Bending to the limit (1mm) with 1.0mm/sec.
<b>Solderability</b>	More than 75% of terminal surface is to be soldered newly	SnAg3.0Cu0.5 solder $245 \pm 5^\circ\text{C}$ , $3 \pm 0.3$ sec. (preheating : $80 \sim 120^\circ\text{C}$ for $10 \sim 30$ sec.)
<b>Resistance to Soldering heat</b>	Capacitance change : within $\pm 20\%$ Tan δ, IR : initial spec.	Solder pot : $270 \pm 5^\circ\text{C}$ , $10 \pm 1$ sec.

	Performance	Test condition
<b>Vibration Test</b>	Capacitance change : within $\pm 20\%$ Tan $\delta$ , IR : initial spec.	Amplitude : 1.5mm From 10Hz to 55Hz (return : 1min.) 2hours $\times$ 3 direction (x, y, z)
<b>Moisture Resistance</b>	Capacitance change : within $\pm 30\%$ Tan $\delta$ : 0.09 max IR : 500Mohm or $25\text{Mohm} \cdot \mu\text{F}$ Whichever is Smaller	With rated voltage 40 $\pm 2^\circ\text{C}$ , 90~95%RH, 500+12/-0hrs
<b>High Temperature Resistance</b>	Capacitance change : within $\pm 30\%$ Tan $\delta$ : 0.09 max IR : 1000Mohm or $50\text{Mohm} \cdot \mu\text{F}$ Whichever is Smaller	With 200% of the rated voltage Max. operating temperature 1000+48/-0hrs
<b>Temperature Cycling</b>	Capacitance change : within $\pm 20\%$ Tan $\delta$ , IR : initial spec.	1 cycle condition Min. operating temperature $\rightarrow 25^\circ\text{C}$ $\rightarrow$ Max. operating temperature $\rightarrow 25^\circ\text{C}$ 5 cycle test

**C. Recommended Soldering method :**

Reflow ( Reflow Peak Temperature : 260 $\pm 0/-5^\circ\text{C}$ , 10sec. Max )

\* For the more detail Specification, Please refer to the Samsung MLCC catalogue.