



REV	DESCRIPTION	DATE
B	OBSOLETE S/S BY 99-1718-1DGU	06/22/01



NOTES:

- 1 MAXIMUM RECOMMENDED STROKE: .500
- 2 FOR USE WITH THE 225/245 TOOL, USE ATTACHMENT P/N 119400 AND STROKE LIMITER 118362.
- 3 FOR USE WITH THE 2500 TOOL, USE ATTACHMENT P/N 119400 AND STROKE LIMITER KIT 119888.
- 4 FOR OTHER TOOLS AND/OR OTHER TOOL AND STROKE COMBINATIONS, CONSULT ENGINEERING DEPARTMENT.
- 5 OPTIONAL DEFLECTOR KIT P/N 122911 AVAILABLE FOR THIS NOSE ASSEMBLY.
- 6 OPTIONAL LOOSE CHUCK JAW KIT P/N 123489 AVAILABLE FOR THIS NOSE ASSEMBLY CONSISTS OF:
122748 CHUCK JAWS
118207 FOLLOWER
505717 SPRING
122449 LOCATER
122448 RETAINING NUT
- 7 ANVIL ASSEMBLY 119415U CONSISTS OF ANVIL HOLDER 119348 AND DRIVING ANVIL 125445-08.



IDENTIFICATION PER SPEC 42-311: ★ ETCH			
HUCK INTERNATIONAL, INC., I.S.D. 1 CORPORATE DRIVE, P.O. BOX 2270 KINGSTON, NEW YORK 12401			
NOSE ASSEMBLY -08 FLAT BLIND RIVET			
DET: MP	CK:	DATE: 12/10/99	SCALE: 2:1
FOC.	B	99-1718-1U	
FAC.			