

Plug-In

Power Splitter/Combiner

2 Way-90° 50Ω 12 to 14 MHz

PSCQ-2-13



CASE STYLE: A01
PRICE: \$18.20 ea. QTY. (1-9)


Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	1W max.

Pin Connections

SUMPORT	1
PORT 1 (+90°)	2
PORT 2 (0°)	5
GROUND	3,4,7,8
CASE GROUND	3,4,7,8
50 OHM TERM EXTERNAL	6

Outline Drawing



Outline Dimensions (inch)

A	B	C	D	E	F
.770	.800	.385	.400	.370	.400
19.56	20.32	9.78	10.16	9.40	10.16
G	H	J	K	wt	
.200	.20	.14	.031	grams	
5.08	5.08	3.56	0.79	5.2	

Features

- low insertion loss, 0.4 dB typ.
- excellent isolation, 29 dB typ.
- excellent phase unbalance, 1 deg. typ.
- excellent VSWR, 1.10:1 typ.
- rugged shielded case

Applications




- modulators
- balanced amplifiers

Splitter Electrical Specifications


FREQ. RANGE (MHz)	ISOLATION (dB)		INSERTION LOSS (dB) Avg. of Coupled Outputs less 3 dB		PHASE UNBALANCE (Degrees)	AMPLITUDE UNBALANCE (dB)
f_L - f_U	Typ.	Min.	Typ.	Max.	Max.	Max.
12-14	29	25	0.4	0.7	3	1.2

Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)		Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR S	VSWR 1	VSWR 2
	S-1	S-2						
12.00	3.61	2.62	0.98	30.73	89.61	1.07	1.08	1.08
12.05	3.58	2.65	0.94	30.69	89.60	1.07	1.08	1.08
12.15	3.55	2.68	0.87	30.68	89.63	1.07	1.08	1.08
12.25	3.51	2.70	0.80	30.66	89.64	1.07	1.08	1.08
12.35	3.47	2.74	0.73	30.64	89.59	1.07	1.08	1.08
12.50	3.41	2.79	0.63	30.60	89.63	1.07	1.08	1.08
12.65	3.36	2.84	0.53	30.57	89.63	1.07	1.08	1.08
12.80	3.31	2.89	0.43	30.53	89.60	1.07	1.08	1.08
12.95	3.26	2.93	0.33	30.51	89.61	1.07	1.08	1.08
13.15	3.19	3.00	0.20	30.45	89.63	1.07	1.08	1.08
13.35	3.13	3.06	0.07	30.42	89.69	1.07	1.08	1.08
13.55	3.06	3.12	0.06	30.38	89.64	1.07	1.08	1.08
13.75	3.01	3.19	0.18	30.35	89.65	1.07	1.08	1.08
13.90	2.96	3.23	0.27	30.32	89.63	1.07	1.08	1.08
14.00	2.93	3.26	0.33	30.30	89.64	1.07	1.08	1.08



electrical schematic



Mini-Circuits®

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

REV. OR
M94664
PSCQ-2-13
HY/TD/CP
060821