


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
FT	0		O	RELEASED	18JUN2003	SW CR
			A	REVISED EC 0G3B-0652-04	13AUG2004	SW CR



1546552-3 AS SHOWN

- ⚠ MATERIALS AND FINISH:
HOUSING: PA 6-6, UL 94 VO-RATED, COLOR: GREEN.
TERMINAL: COPPER ALLOY, TIN PLATED.
CLAMP: COPPER ALLOY, NICKEL PLATED.
CLAMPING SCREW: COPPER ALLOY, NICKEL PLATED.
2. WIRE SIZE RANGE: 16-28 AWG.
3. CURRENT RATING: 12A, 150V
OPERATING TEMPERATURE: -40°C TO +110°C
4. SUITABLE FOR 2.4mm MAX PC BOARD THICKNESS.

95.25	25	2-1546552-5
91.44	24	2-1546552-4
87.63	23	2-1546552-3
83.82	22	2-1546552-2
80.01	21	2-1546552-1
76.20	20	2-1546552-0
72.39	19	1-1546552-9
68.58	18	1-1546552-8
64.77	17	1-1546552-7
60.96	16	1-1546552-6
57.15	15	1-1546552-5
53.34	14	1-1546552-4
49.53	13	1-1546552-3
45.72	12	1-1546552-2
41.91	11	1-1546552-1
38.10	10	1-1546552-0
34.29	9	1546552-9
30.48	8	1546552-8
26.67	7	1546552-7
22.86	6	1546552-6
19.05	5	1546552-5
15.24	4	1546552-4
11.43	3	1546552-3
7.62	2	1546552-2
L	NO OF POSN	PART NUMBER

RECOMMENDED PC BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN S. WELDON	18JUN2003	BUCHANAN Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS:		CHK C. RICHARD	18JUN2003		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD C. RICHARD	18JUN2003	NAME TERMINAL BLOCK, PCB MOUNT, STRAIGHT, 8.5mm PROFILE, SIDE WIRE ENTRY, 3.81mm PITCH	
	0 PLC ± 1 PLC ±0.3 2 PLC ±0.25 3 PLC ±0.000 4 PLC ±0.0000 ANGLES ± FINISH	PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		SIZE A2	CAGE CODE 00779
MATERIAL ⚠ -	⚠ -	CUSTOMER DRAWING		DRAWING NO 1546552	RESTRICTED TO -
			SCALE 6:1	SHEET 1	OF 1
				REV A	