


SWITCHING APPLICATION.  
INTERFACE CIRCUIT AND DRIVER CIRCUIT APPLICATION.

### FEATURES


- With Built-in Bias Resistors.
- Simplify Circuit Design.
- Reduce a Quantity of Parts and Manufacturing Process.
- High Packing Density.

### EQUIVALENT CIRCUIT



### BIAS RESISTOR VALUES


| TYPE NO. | R1(k $\Omega$ ) | R2(k $\Omega$ ) |
|----------|-----------------|-----------------|
| KRA721U  | 4.7             | 4.7             |
| KRA722U  | 10              | 10              |
| KRA723U  | 22              | 22              |
| KRA724U  | 47              | 47              |
| KRA725U  | 2.2             | 47              |
| KRA726U  | 4.7             | 47              |



| DIM | MILLIMETERS          |
|-----|----------------------|
| A   | 2.00 $\pm$ 0.20      |
| A1  | 1.3 $\pm$ 0.1        |
| B   | 2.1 $\pm$ 0.1        |
| B1  | 1.25 $\pm$ 0.1       |
| C   | 0.65                 |
| D   | 0.2 $\pm$ 0.10/-0.05 |
| G   | 0-0.1                |
| H   | 0.9 $\pm$ 0.1        |
| T   | 0.15 $\pm$ 0.1/-0.05 |

US6

### EQUIVALENT CIRCUIT (TOP VIEW)



### MAXIMUM RATING (Ta=25°C)


| CHARACTERISTIC            |                | SYMBOL           | RATING    | UNIT |
|---------------------------|----------------|------------------|-----------|------|
| Output Voltage            | KRA721U ~ 726U | V <sub>O</sub>   | -50       | V    |
| Input Voltage             | KRA721U        | V <sub>I</sub>   | -20, 10   | V    |
|                           | KRA722U        |                  | -30, 10   |      |
|                           | KRA723U        |                  | -40, 10   |      |
|                           | KRA724U        |                  | -40, 10   |      |
|                           | KRA725U        |                  | -12, 5    |      |
|                           | KRA726U        |                  | -20, 5    |      |
| Output Current            | KRA721U ~ 726U | I <sub>O</sub>   | -100      | mA   |
| Power Dissipation         |                | P <sub>D</sub> * | 200       | mW   |
| Junction Temperature      |                | T <sub>j</sub>   | 150       | °C   |
| Storage Temperature Range |                | T <sub>stg</sub> | -55 ~ 150 | °C   |

\* Total Rating.

### MARK SPEC

| TYPE | KRA721U | KRA722U | KRA723U | KRA724U | KRA725U | KRA726U |
|------|---------|---------|---------|---------|---------|---------|
| MARK | JA      | JB      | JC      | JD      | JE      | JF      |

Marking Type Name



# KRA721U~KRA726U

## ELECTRICAL CHARACTERISTICS (Ta=25℃)

| CHARACTERISTIC         |                | SYMBOL       | TEST CONDITION              | MIN. | TYP.  | MAX.  | UNIT |
|------------------------|----------------|--------------|-----------------------------|------|-------|-------|------|
| Output Cut-off Current | KRA721U ~ 726U | $I_{O(OFF)}$ | $V_O = -50V, V_I = 0$       | -    | -     | -500  | nA   |
| DC Current Gain        | KRA721U        | $G_I$        | $V_O = -5V, I_O = -10mA$    | 30   | 55    | -     |      |
|                        | KRA722U        |              |                             | 50   | 80    | -     |      |
|                        | KRA723U        |              |                             | 70   | 120   | -     |      |
|                        | KRA724U        |              |                             | 80   | 200   | -     |      |
|                        | KRA725U        |              |                             | 80   | 200   | -     |      |
|                        | KRA726U        |              |                             | 80   | 200   | -     |      |
| Output Voltage         | KRA721U ~ 726U | $V_{O(ON)}$  | $I_O = -10mA, I_I = -0.5mA$ | -    | -0.1  | -0.3  | V    |
| Input Voltage (ON)     | KRA721U        | $V_{I(ON)}$  | $V_O = -0.2V, I_O = -5mA$   | -    | -1.5  | -2.0  | V    |
|                        | KRA722U        |              |                             | -    | -1.8  | -2.4  |      |
|                        | KRA723U        |              |                             | -    | -2.1  | -3.0  |      |
|                        | KRA724U        |              |                             | -    | -2.8  | -5.0  |      |
|                        | KRA725U        |              |                             | -    | -0.8  | -1.1  |      |
|                        | KRA726U        |              |                             | -    | -0.9  | -1.3  |      |
| Input Voltage (OFF)    | KRA721U ~ 724U | $V_{I(OFF)}$ | $V_O = -5V, I_O = -0.1mA$   | -1.0 | -1.2  | -     | V    |
|                        | KRA725U ~ 726U |              |                             | -0.5 | -0.65 | -     |      |
| Transition Frequency   | KRA721U ~ 726U | $f_T^*$      | $V_O = -10V, I_O = -5mA$    | -    | 200   | -     | MHz  |
| Input Current          | KRA721U        | $I_I$        | $V_I = -5V$                 | -    | -     | -1.8  | mA   |
|                        | KRA722U        |              |                             | -    | -     | -0.88 |      |
|                        | KRA723U        |              |                             | -    | -     | -0.36 |      |
|                        | KRA724U        |              |                             | -    | -     | -0.18 |      |
|                        | KRA725U        |              |                             | -    | -     | -3.6  |      |
|                        | KRA726U        |              |                             | -    | -     | -1.8  |      |







Note : \* Characteristic of Transistor Only.

# KRA721U~KRA726U







## ELECTRICAL CHARACTERISTICS (Ta=25℃)

| CHARACTERISTIC |              |         | SYMBOL           | TEST CONDITION                                                     | MIN. | TYP. | MAX. | UNIT |
|----------------|--------------|---------|------------------|--------------------------------------------------------------------|------|------|------|------|
| Switching Time | Rise Time    | KRA721U | t <sub>r</sub>   | V <sub>O</sub> =-5V<br>V <sub>IN</sub> =-5V<br>R <sub>L</sub> =1kΩ | -    | 0.07 | -    | μS   |
|                |              | KRA722U |                  |                                                                    | -    | 0.06 | -    |      |
|                |              | KRA723U |                  |                                                                    | -    | 0.2  | -    |      |
|                |              | KRA724U |                  |                                                                    | -    | 0.24 | -    |      |
|                |              | KRA725U |                  |                                                                    | -    | 0.02 | -    |      |
|                |              | KRA726U |                  |                                                                    | -    | 0.07 | -    |      |
|                | Storage Time | KRA721U | t <sub>stg</sub> |                                                                    | -    | 1.1  | -    |      |
|                |              | KRA722U |                  |                                                                    | -    | 1.1  | -    |      |
|                |              | KRA723U |                  |                                                                    | -    | 1.1  | -    |      |
|                |              | KRA724U |                  |                                                                    | -    | 1.1  | -    |      |
|                |              | KRA725U |                  |                                                                    | -    | 1.1  | -    |      |
|                |              | KRA726U |                  |                                                                    | -    | 1.1  | -    |      |
|                | Fall Time    | KRA721U | t <sub>f</sub>   |                                                                    | -    | 0.15 | -    |      |
|                |              | KRA722U |                  |                                                                    | -    | 0.24 | -    |      |
|                |              | KRA723U |                  |                                                                    | -    | 0.38 | -    |      |
|                |              | KRA724U |                  |                                                                    | -    | 0.63 | -    |      |
|                |              | KRA725U |                  |                                                                    | -    | 0.1  | -    |      |
|                |              | KRA726U |                  |                                                                    | -    | 0.2  | -    |      |

# KRA721U~KRA726U



# KRA721U~KRA726U



# KRA721U~KRA726U

