

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

ALL RIGHTS RESERVED.

LOC
JDIST
-

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

P REVISED PER ECO-11-005294

11APR11

RK HMR

19.35±0.05

13.3±0.05

8.9±0.05

スケール 2:1

E±0.05

パネル加工推奨寸法図

RECOMMENDED PANEL LAYOUT

(適用パネル厚: 1.0-2.0)

(APPLICABLE PANEL THICKNESS: 1.0-2.0)

10 REF

1.5 TYP

1 2 3 4
-AMP

6

注記

1: 材料: ハウジング: ガラス入り熱可塑性ポリエステル樹脂, 94V-0, 黒

コンタクト: 銅合金

2: メッキ: コンタクト: 全面 Ni 下地

接点部: 0.2μm MIN 金メッキ

3: 金属パネルの場合、コネクタ取付方向を/ ンチ加工方向にしてください。

4: プラスチックパネルの場合、穴端部に R 無き様ご配慮ください。

NOTE

1: MATERIAL. HOUSING: GLASS FILLED THERMOPLASTIC, 94V-0, BLACK
CONTACT: COPPER ALLOY

2: FINISH. UNDERPLATE: Ni 1.27μm min.

CONTACT AREA: Au 0.2μm min.

3: INSERT CONN. FROM PRESS DIRECTION SIDE FOR METAL PANEL.

4: EDGE OF THICKNESS WAY MUST NOT ROUND FOR MOLDED PANEL.

2xN=A

2

1

6.5

9.8

B

C

30±0.5

13

JUNCTION HOUSING B

JUNCTION HOUSING A

D

8.6

5.2

3.1

JUNCTION CONTACT

22.5 REF

F/H	16.1	15.8	6.75	8.9	6	3	4	5-1473574-4
F/H	14.1	13.8	5.75	6.9	4	2	3	5-1473574-3
P/M	16.1	15.8	6.75	8.9	6	3	4	1473574-4
P/M	14.1	13.8	5.75	6.9	4	2	3	1473574-3
TYPE	E	D	C	B	A	N	POS	PART NUMBER

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN D. MITSUGI	10SEP2001
		0 PLC	±	CHK S. MANABE	10SEP2001
		1 PLC	±	APVD S. MANABE	10SEP2001
		2 PLC	±	PRODUCT SPEC	
		3 PLC	±	108-5765	
		4 PLC	±	APPLICATION SPEC	
MATERIAL		ANGLES	±	-	
FINISH		-	-	WEIGHT	-
CUSTOMER DRAWING					

TE

TE Connectivity

JUNCTION BOX (4D)
FOR E-CON
- RITS CONN. -

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C=1473574	-
SCALE	2:1	SHEET	OF
REV	P		

-1, -2 P/M TYPE

スケール 2:1

5- -1, 5- -2 F/H TYPE

スケール 2:1