



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AJ	16		01	REVISED PER ECO-05-007704	02SEP05	BM	KW

- ⚠ CONTACT CRIMP TOOLING: CRIMP TOOL M22520/2-01 WITH POSITIONER DMC K997 SELECTOR SETTING #4 FOR RG-174/U, RG-188/U & RG-316/U SINGLE AND DOUBLE SHIELDED CABLE.
- ⚠ FERRULE CRIMP TOOLING: CRIMP TOOL M22520/5-01 WITH DIE SET M22520/5-35B OR USE A 3.25 [.128] X 10.16 [.400] HEX DIE SET.
3. PRODUCT DESIGNED TO MEET PRODUCT SPECIFICATION 108-1574.
4. INSTRUCTION SHEET: 408-4032



RECOMMENDED STRIP LENGTHS

⚠ ⚠	RG-174, -188, & -316/U	9-446556-1	447842-3	447963-2	5447648-3
CRIMP TOOLING	CABLE	③ FERRULE QTY=1	② CONTACT QTY=1	① JACK ASSY QTY=1	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. VARELA - 31JAN2005	tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608		
DIMENSIONS: mm [INCHES]		CHK J. HAVENER 31JAN2005			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D. CAMELIO 31JAN2005	NAME JACK, HEX CRIMP, COMMERCIAL, SMA		
	0 PLC ± -	PRODUCT SPEC			
	1 PLC ± -	APPLICATION SPEC			
MATERIAL	2 PLC ± 0.40 [.016]	—	SIZE	CAGE CODE	DRAWING NO
	3 PLC ± -	—	A2	00779	C=5447648
FINISH	4 PLC ± -	WEIGHT	—	RESTRICTED TO	—
	—	CUSTOMER DRAWING	SCALE 8:1	SHEET 1 OF 1	REV 01