



### FEATURES:

- RoHS compliant
- High efficiency up to 82%
- Low profile plastic package
- 7 pin SIP package
- Operating temperature -40°C to + 105°C
- Continuous short circuit protection
- Pin compatible with multiple manufacturers
- Up to 3000VDC Isolation

### Models

#### Single output



| Model               | Input Voltage (V) | Output Voltage (V) | Output Current max (mA) | Isolation (VDC) | Input Current Full Load   No Load (mA) |    | Max. Capacitive Load (μF) | Efficiency Typ. (%) |
|---------------------|-------------------|--------------------|-------------------------|-----------------|----------------------------------------|----|---------------------------|---------------------|
| AM1DS-0303S-NZ*     | 3.0-3.6           | 3.3                | 303                     | 1500            | 415                                    | 25 | 220                       | 78                  |
| AM1DS-0305S-NZ*     | 3.0-3.6           | 5                  | 200                     | 1500            | 388                                    | 25 | 220                       | 79                  |
| AM1DS-0505S-NZ      | 4.5-5.5           | 5                  | 200                     | 1500            | 250                                    | 20 | 220                       | 80                  |
| AM1DS-0505SJZ*      | 4.5-5.5           | 5                  | 200                     | 1500            | 257                                    | 10 | 2400                      | 82                  |
| AM1DS-0509S-NZ      | 4.5-5.5           | 9                  | 112                     | 1500            | 250                                    | 20 | 220                       | 80                  |
| AM1DS-0512S-NZ      | 4.5-5.5           | 12                 | 83                      | 1500            | 248                                    | 20 | 220                       | 81                  |
| AM1DS-0515S-NZ      | 4.5-5.5           | 15                 | 67                      | 1500            | 248                                    | 20 | 220                       | 81                  |
| AM1DS-0524S-NZ ‡    | 4.5-5.5           | 24                 | 42                      | 1500            | 248                                    | 20 | 220                       | 81                  |
| AM1DS-1205S-NZ      | 10.8-13.2         | 5                  | 200                     | 1500            | 111                                    | 15 | 220                       | 80                  |
| AM1DS-1209S-NZ      | 10.8-13.2         | 9                  | 112                     | 1500            | 92                                     | 15 | 220                       | 80                  |
| AM1DS-1212S-NZ      | 10.8-13.2         | 12                 | 83                      | 1500            | 92                                     | 15 | 220                       | 81                  |
| AM1DS-1215S-NZ      | 10.8-13.2         | 15                 | 67                      | 1500            | 90                                     | 15 | 220                       | 81                  |
| AM1DS-1515S-NZ*     | 13.5-16.5         | 15                 | 67                      | 1500            | 84                                     | 10 | 220                       | 80                  |
| AM1DS-2403S-NZ*     | 21.6-26.4         | 3.3                | 303                     | 1500            | 56                                     | 7  | 220                       | 79                  |
| AM1DS-2405S-NZ      | 21.6-26.4         | 5                  | 200                     | 1500            | 51                                     | 7  | 220                       | 79                  |
| AM1DS-2412S-NZ      | 21.6-26.4         | 12                 | 83                      | 1500            | 52                                     | 7  | 220                       | 81                  |
| AM1DS-2415S-NZ      | 21.6-26.4         | 15                 | 67                      | 1500            | 52                                     | 7  | 220                       | 81                  |
| AM1DS-2424S-NZ ‡    | 21.6-26.4         | 24                 | 42                      | 1500            | 52                                     | 7  | 220                       | 82                  |
| AM1DS-0305SH30-NZ*  | 3.0-3.6           | 5                  | 200                     | 3000            | 388                                    | 25 | 220                       | 79                  |
| AM1DS-0505SH30-NZ   | 4.5-5.5           | 5                  | 200                     | 3000            | 250                                    | 20 | 220                       | 80                  |
| AM1DS-0509SH30-NZ   | 4.5-5.5           | 9                  | 112                     | 3000            | 250                                    | 20 | 220                       | 80                  |
| AM1DS-0512SH30-NZ   | 4.5-5.5           | 12                 | 83                      | 3000            | 248                                    | 20 | 220                       | 80                  |
| AM1DS-0515SH30-NZ   | 4.5-5.5           | 15                 | 67                      | 3000            | 248                                    | 20 | 220                       | 81                  |
| AM1DS-0524SH30-NZ ‡ | 4.5-5.5           | 24                 | 42                      | 3000            | 248                                    | 20 | 220                       | 81                  |
| AM1DS-1205SH30-NZ   | 10.8-13.2         | 5                  | 200                     | 3000            | 111                                    | 15 | 220                       | 80                  |
| AM1DS-1209SH30-NZ   | 10.8-13.2         | 9                  | 112                     | 3000            | 111                                    | 15 | 220                       | 80                  |
| AM1DS-1212SH30-NZ   | 10.8-13.2         | 12                 | 83                      | 3000            | 92                                     | 15 | 220                       | 81                  |
| AM1DS-1215SH30-NZ   | 10.8-13.2         | 15                 | 67                      | 3000            | 92                                     | 15 | 220                       | 81                  |
| AM1DS-1224SH30-NZ ‡ | 10.8-13.2         | 24                 | 42                      | 3000            | 92                                     | 15 | 220                       | 80                  |
| AM1DS-2405SH30-NZ   | 21.6-26.4         | 5                  | 200                     | 3000            | 51                                     | 7  | 220                       | 79                  |
| AM1DS-2409SH30-NZ   | 21.6-26.4         | 9                  | 112                     | 3000            | 51                                     | 7  | 200                       | 80                  |
| AM1DS-2412SH30-NZ   | 21.6-26.4         | 12                 | 83                      | 3000            | 52                                     | 7  | 220                       | 81                  |
| AM1DS-2415SH30-NZ   | 21.6-26.4         | 15                 | 67                      | 3000            | 52                                     | 7  | 220                       | 81                  |
| AM1DS-2424SH30-NZ ‡ | 21.6-26.4         | 24                 | 42                      | 3000            | 52                                     | 7  | 220                       | 82                  |

### Models

#### Dual output

| Model           | Input Voltage (V) | Output Voltage (V) | Output Current max (mA) | Isolation (VDC) | Input Current Full Load   No Load (mA) |    | Max. Capacitive Load (μF) | Efficiency Typ. (%) |
|-----------------|-------------------|--------------------|-------------------------|-----------------|----------------------------------------|----|---------------------------|---------------------|
| AM1DS-0305D-NZ* | 2.97-3.63         | ±5                 | ±100                    | 1500            | 274                                    | 20 | 100                       | 78                  |
| AM1DS-0312D-NZ* | 2.97-3.63         | ±12                | ±42                     | 1500            | 248                                    | 20 | 100                       | 78                  |
| AM1DS-0505D-NZ  | 4.5-5.5           | ±5                 | ±100                    | 1500            | 274                                    | 20 | 100                       | 80                  |
| AM1DS-0505D-JZ  | 4.5-5.5           | ±5                 | ±100                    | 1500            | 286                                    | 10 | 1200                      | 82                  |
| AM1DS-0509D-NZ  | 4.5-5.5           | ±9                 | ±56                     | 1500            | 250                                    | 20 | 100                       | 80                  |
| AM1DS-0512D-NZ  | 4.5-5.5           | ±12                | ±42                     | 1500            | 248                                    | 20 | 100                       | 80                  |
| AM1DS-0515D-NZ  | 4.5-5.5           | ±15                | ±34                     | 1500            | 248                                    | 20 | 100                       | 81                  |

|                     |           |     |      |      |     |    |     |    |
|---------------------|-----------|-----|------|------|-----|----|-----|----|
| AM1DS-0524D-NZ ‡    | 4.5-5.5   | ±24 | ±21  | 1500 | 248 | 20 | 100 | 81 |
| AM1DS-1205D-NZ      | 10.8-13.2 | ±5  | ±100 | 1500 | 92  | 15 | 100 | 80 |
| AM1DS-1212D-NZ      | 10.8-13.2 | ±12 | ±42  | 1500 | 92  | 15 | 100 | 81 |
| AM1DS-1215D-NZ      | 10.8-13.2 | ±15 | ±34  | 1500 | 90  | 15 | 100 | 81 |
| AM1DS-1512D-NZ*     | 13.5-16.5 | ±12 | ±42  | 1500 | 92  | 15 | 100 | 80 |
| AM1DS-1515D-NZ      | 13.5-16.5 | ±15 | ±34  | 1500 | 84  | 10 | 100 | 80 |
| AM1DS-2405D-NZ      | 21.6-26.4 | ±5  | ±100 | 1500 | 53  | 7  | 100 | 79 |
| AM1DS-2412D-NZ      | 21.6-26.4 | ±12 | ±42  | 1500 | 51  | 7  | 100 | 81 |
| AM1DS-2415D-NZ      | 21.6-26.4 | ±15 | ±34  | 1500 | 51  | 7  | 100 | 82 |
| AM1DS-2424D-NZ ‡    | 21.6-26.4 | ±24 | ±21  | 1500 | 51  | 7  | 100 | 82 |
| AM1DS-0505DH30-NZ   | 4.5-5.5   | ±5  | ±100 | 3000 | 274 | 20 | 100 | 80 |
| AM1DS-0509DH30-NZ   | 4.5-5.5   | ±9  | ±56  | 3000 | 250 | 20 | 100 | 80 |
| AM1DS-0512DH30-NZ   | 4.5-5.5   | ±12 | ±42  | 3000 | 248 | 20 | 100 | 80 |
| AM1DS-0515DH30-NZ   | 4.5-5.5   | ±15 | ±34  | 3000 | 250 | 20 | 100 | 81 |
| AM1DS-0524DH30-NZ ‡ | 4.5-5.5   | ±24 | ±21  | 3000 | 250 | 20 | 100 | 81 |
| AM1DS-1205DH30-NZ   | 10.8-13.2 | ±5  | ±100 | 3000 | 248 | 20 | 100 | 81 |
| AM1DS-1212DH30-NZ   | 10.8-13.2 | ±12 | ±42  | 3000 | 92  | 15 | 100 | 81 |
| AM1DS-1215DH30-NZ   | 10.8-13.2 | ±15 | ±34  | 3000 | 90  | 15 | 100 | 79 |
| AM1DS-1224DH30-NZ ‡ | 10.8-13.2 | ±24 | ±21  | 3000 | 90  | 15 | 100 | 79 |
| AM1DS-2405DH30-NZ   | 21.6-26.4 | ±5  | ±100 | 3000 | 53  | 7  | 100 | 81 |
| AM1DS-2409DH30-NZ   | 21.6-26.4 | ±9  | ±56  | 3000 | 53  | 7  | 100 | 81 |
| AM1DS-2412DH30-NZ   | 21.6-26.4 | ±12 | ±42  | 3000 | 51  | 7  | 100 | 81 |
| AM1DS-2415DH30-NZ   | 21.6-26.4 | ±15 | ±34  | 3000 | 51  | 7  | 100 | 82 |
| AM1DS-2424DH30-NZ ‡ | 21.6-26.4 | ±24 | ±21  | 3000 | 51  | 7  | 100 | 82 |

‡ With Momentary short circuit protection of 1 second

\* Reference in the Safety Table

NOTE: All specifications in this datasheet are measured at an ambient temperature of 25°C, humidity<75%, nominal input voltage and at rated output load unless otherwise specified.

## Input Specifications

| Parameters                          | Nominal   | Typical              | Maximum | Units |
|-------------------------------------|-----------|----------------------|---------|-------|
| Voltage range                       | 3.3       | 2.97–3.63 or 3.0-3.6 |         | VDC   |
|                                     | 5         | 4.5-5.5              |         |       |
|                                     | 12        | 10.8-13.2            |         |       |
|                                     | 15        | 13.5-16.5            |         |       |
|                                     | 24        | 21.6-26.4            |         |       |
| Filter                              | Capacitor |                      |         |       |
| Absolute Maximum Rating             | 3.3       |                      | 7       | VDC   |
|                                     | 5         |                      | 9       |       |
|                                     | 12        |                      | 18      |       |
|                                     | 15        |                      | 21      |       |
|                                     | 24        |                      | 30      |       |
| Peak Input Voltage time             |           |                      | 1       | s     |
| No Load Input Current               |           |                      | 50      | mA    |
| AM1DS-0505SJZ input no load current |           | 5                    | 10      | mA    |

## Isolation Specifications

| Parameters         | Conditions | Typical | Rated      | Units |
|--------------------|------------|---------|------------|-------|
| Tested I/O voltage | 60 sec     |         | 1500, 3000 | VDC   |
| Resistance         |            | > 1000  |            | MOhm  |
| Capacitance        |            | 20      |            | pF    |

## Output Specifications

| Parameters               | Conditions                       | Typical                                   | Maximum | Units    |
|--------------------------|----------------------------------|-------------------------------------------|---------|----------|
| Voltage accuracy         |                                  | ±5                                        |         | %        |
| Short Circuit protection | Continuous, unless marked with ‡ |                                           |         |          |
| Short circuit restart    | Auto recovery                    |                                           |         |          |
| Line voltage regulation  | For 1.0% change of Vin           | ±1.2                                      |         | % of Vin |
| Load voltage regulation  | load 10~100%                     | 10%                                       |         | %        |
| Temperature coefficient  |                                  | ±0.02                                     |         | %/°C     |
| Ripple & Noise           | 20MHz Bandwidth                  | (output 3.3/5/12) 30<br>(output 15/24) 60 |         | mV p-p   |
| Minimum Load Current     |                                  | 10                                        |         | % of Max |


## General Specifications

| Parameters                                                | Conditions                                             | Typical     | Maximum | Units |
|-----------------------------------------------------------|--------------------------------------------------------|-------------|---------|-------|
| Switching frequency                                       | 100% load                                              | 100 - 300   |         | KHz   |
| Switching frequency (for part number with suffix JZ)      | 100% load                                              | 270         |         | KHz   |
| Operating temperature                                     | With derating above 85°C                               | -40 to +105 |         | °C    |
| Storage temperature                                       |                                                        | -55 to +125 |         | °C    |
| Maximum case temperature                                  |                                                        |             | 100     | °C    |
| Derating                                                  | Not-Required                                           |             |         | %/°C  |
| Cooling                                                   | Free air convection                                    |             |         |       |
| Humidity                                                  |                                                        |             | 95      | % RH  |
| Case material                                             | Non-conductive black plastic (UL94V-0 rated)           |             |         |       |
| Weight                                                    | 2.3                                                    |             |         | g     |
| Dimensions (L x W x H)                                    | 0.76 x 0.24 x 0.37inches 19.5 x 6.00 x 9.35mm          |             |         |       |
| Dimensions (L x W x H)<br>For part numbers with suffix JZ | 0.77 x 0.24 x 0.4inches 19.65 x 6.00 x 10.16mm         |             |         |       |
| MTBF                                                      | >3,500,000hrs (MIL-HDBK -217F, Ground Benign, t=+25°C) |             |         |       |
| Maximum soldering temperature                             | 1.5 mm from case for 10sec                             |             | 300     | °C    |

## Safety Specifications

| Parameters       |                                  |                                                                               |
|------------------|----------------------------------|-------------------------------------------------------------------------------|
| Agency approvals | cULus                            |                                                                               |
| Standards        | Information technology Equipment | UL 60950-1 (except the models marked with *)<br>UL 62368 (AM1DS-0505SJZ only) |

## Typical Recommended Circuit




| Vin       | Cin | Vout      | Cout        | Vout (Dual)           | Cout (Dual)  |
|-----------|-----|-----------|-------------|-----------------------|--------------|
| 3.3 & 5 V | 4.7 | 3.3 & 5 V | 10 $\mu$ F  | $\pm$ 3.3 & $\pm$ 5 V | 4.7 $\mu$ F  |
| 12 V      | 2.2 | 12 V      | 2.2 $\mu$ F | $\pm$ 12 V            | 1 $\mu$ F    |
| 15 V      | 2.2 | 15 & 24 V | 1 $\mu$ F   | $\pm$ 15 & $\pm$ 24 V | 0.47 $\mu$ F |
| 24 V      | 1   | -         | -           |                       |              |


## Pin Out Specifications

| Pin | 1500 VDC   |            | 3000VDC    |            |
|-----|------------|------------|------------|------------|
|     | Single     | Dual       | Single     | Dual       |
| 1   | + V Input  | + V Input  | + V Input  | + V Input  |
| 2   | - V Input  | - V Input  | - V Input  | - V Input  |
| 4   | - V Output | - V Output | No pin     | No pin     |
| 5   | No pin     | Common     | - V Output | - V Output |
| 6   | + V Output | + V Output | No pin     | Common     |
| 7   | No pin     | No pin     | + V Output | + V Output |


## Dimensions




### Dimensions for part numbers with suffix JZ




### Derating




### EMI Recommended Circuit (Class B)




### Load Accuracy Tolerance Graph




### Typical Efficiency Example Charts




**AM1DS-0505S-NZ Efficiency vs. Loading**




**AM1DS-1205S-NZ Efficiency vs. Loading**



**AM1DS-1515S-NZ Efficiency vs. Loading**





**NOTE:** **1.** Datasheets are updated as needed and as such, specifications are subject to change without notice. Once printed or downloaded, datasheets are no longer controlled by Aimtec; refer to [www.aimtec.com](http://www.aimtec.com) for the most current product specifications. **2.** Product labels shown, including safety agency certifications on labels, may vary based on the date manufactured. **3.** Mechanical drawings and specifications are for reference only. **4.** All specifications are measured at an ambient temperature of 25°C, humidity<75%, nominal input voltage and at rated output load unless otherwise specified. **5.** Aimtec may not have conducted destructive testing or chemical analysis on all internal components and chemicals at the time of publishing this document. CAS numbers and other limited information are considered proprietary and may not be available for release. **6.** This product is not designed for use in critical life support systems, equipment used in hazardous environments, nuclear control systems or other such applications which necessitate specific safety and regulatory standards other the ones listed in this datasheet. **7.** Warranty is in accordance with Aimtec's standard Terms of Sale available at [www.aimtec.com](http://www.aimtec.com).