






2176	4	3	2	1
PART NO.	ENG. NO.	DESCRIPTION		
05-06-0301	2176-T	TIN PLATE		
05-06-0303	2176-AT	WITHOUT DETENT, TIN PLATED		
NOT TOOLED	X-2176-999A	WITHOUT DETENT, UNPLATED		
05-06-0302	2176-(P90)IL	WITH DETENT, PLATED, LOOSE		
05-06-0304	2176-(P90)IAL	WITHOUT DETENT, PLATED, LOOSE		




SECTION B-B



SECTION A-A

SCALE 8:1



DETENT LOCATION

SCALE 8:1

NOTES:

1. CRIMP FOR #14 THRU #22 GA. WIRE, ALSO (2) #18 GA. WIRE WITH .03(0.79) THK. INSULATION.
2. MATERIAL: .010/(0.25) THK. 70/30 BRASS ALLOY. PRE-TIN PLATED.
3. PRODUCT SPECIFICATION 05-06-1 APPLIES.

DIMENSIONS SHOWN (METRIC) INCH		UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR ± 1/2°		TITLE		TERM FOR .020/(0.51) X .187/(4.75) SPADE		SHEET NO. 1 OF 1		DATE 92/10/26	
3 PLACE ± .010		METRIC ---		SEE CHART		MOLEX INCORPORATED		U.S.A.		REV. CP	
2 PLACE ± .014		± 0.25		SCALE 8:1		FILE NAME SD2176X1		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.		SIZE	
1 PLACE ---		± 0.35		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING NO. SD-2176-*		DIV.		CP	