

MITSUBISHI LSTTLs M74LS375P

4-BIT BISTABLE LATCH

DESCRIPTION

The M74LS375P is a semiconductor integrated circuit containing 4 bistable latch circuits and is provided with outputs Q and $\bar{Q}$.

FEATURES

- Enable inputs common to two circuits each
- Q and $\bar{Q}$ outputs
- pin 8 GND, pin 16 V_{CC}
- Wide operating temperature range ($T_a = -20 \sim +75^\circ\text{C}$)

APPLICATION

General purpose, for use in industrial and consumer equipment.

FUNCTIONAL DESCRIPTION

This device contains 4 D-type latch circuits and is provided with enable inputs E common to 2 circuits each. When E is high, the information from the data input D appears in the outputs Q and $\bar{Q}$. When the D signal changes, the signal that appears in outputs Q and $\bar{Q}$ also changes. When E changes from high to low, the status of D immediately before the change is latched. While E is low, the status of Q and $\bar{Q}$ does not change even if D is changed.

This IC has the same functions and electrical characteristics as M74LS75P and differs only in its pin configuration.


FUNCTION TABLE (Note 1)

E	D	Q	$\bar{Q}$
H	H	H	L
H	L	L	H
L	X	Q^0	$\bar{Q}^0$

Note 1 $Q^0, \bar{Q}^0$: Level of Q and $\bar{Q}$ before the indicated steady-state input conditions were established.


X: Irrelevant

PIN CONFIGURATION (TOP VIEW)



Outline 16P4

BLOCK DIAGRAM (EACH LATCH)



ABSOLUTE MAXIMUM RATINGS ($T_a = -20 \sim +75^\circ\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Limits	Unit
V_{CC}	Supply voltage		$-0.5 \sim +7$	V
V_I	Input voltage		$-0.5 \sim +15$	V
V_O	Output voltage	High-level state	$-0.5 \sim V_{CC}$	V
T_{opr}	Operating free-air ambient temperature range		$-20 \sim +75$	$^\circ\text{C}$
T_{stg}	Storage temperature range		$-65 \sim +150$	$^\circ\text{C}$

4-BIT BISTABLE LATCH

RECOMMENDED OPERATING CONDITIONS (Ta = -20 ~ +75℃, unless otherwise noted)

Symbol	Parameter		Limits			Unit
			Min	Typ	Max	
V _{CC}	Supply voltage		4.75	5	5.25	V
I _{OH}	High-level output current	V _{OH} ≥ 2.7V	0		-400	μA
I _{OL}	Low-level output current	V _{OL} ≤ 0.4V	0		4	mA
		V _{OL} ≤ 0.5V	0		8	mA

ELECTRICAL CHARACTERISTICS (Ta = -20 ~ +75℃, unless otherwise noted)


Symbol	Parameter		Test conditions	Limits			Unit
				Min	Typ *	Max	
V _{IH}	High-level input voltage			2			V
V _{IL}	Low-level input voltage					0.8	V
V _{IC}	Input clamp voltage					-1.5	V
V _{OH}	High-level output voltage		V _{CC} = 4.75V, I _{IC} = -18mA V _{CC} = 4.75V, V _I = 0.8V V _I = 2V, I _{OH} = -400μA	2.7	3.5		V
V _{OL}	Low-level output voltage		V _{CC} = 4.75V V _I = 0.8V, V _I = 2V		0.25	0.4	V
			I _{OL} = 4mA I _{OL} = 8mA		0.35	0.5	V
I _{IH}	High-level input current	D	V _{CC} = 5.25V V _I = 2.7V			20	μA
		E				80	μA
		D	V _{CC} = 5.25V V _I = 10V			0.1	mA
		E				0.4	mA
I _{IL}	Low-level input current	D	V _{CC} = 5.25V V _I = 0.4V			-0.4	mA
		E				-1.6	mA
I _{OS}	Short-circuit output current (Note 2)		V _{CC} = 5.25V, V _O = 0V	-20		-100	mA
I _{CC}	Supply current		V _{CC} = 5.25V (Note 3)		6.3	12	mA

* : All typical values are at V_{CC} = 5V, Ta = 25℃
Note 2: All measurements should be done quickly and not more than one output should be shorted at a time.
Note 3: I_{CC} is measured with all inputs at 0V.

SWITCHING CHARACTERISTICS (V_{CC} = 5V, Ta = 25℃, unless otherwise noted)

Symbol	Parameter	Test conditions	Limits			Unit
			Min	Typ	Max	
t _{PLH}	Low-to-high-level, high-to-low-level output propagation time, from input D to output Q	C _L = 15pF (Note 4)		12	27	ns
t _{PHL}				8	17	ns
t _{PLH}	Low-to-high-level, high-to-low-level output propagation time, from input D to output Q̅			10	20	ns
t _{PHL}				6	15	ns
t _{PLH}	Low-to-high-level, high-to-low-level output propagation time, from input E to output Q			13	27	ns
t _{PHL}				12	25	ns
t _{PLH}	Low-to-high-level, high-to-low-level output propagation time, from input E to output Q̅			12	30	ns
t _{PHL}				6	15	ns

Note 4: Measurement circuit




- (1) The pulse generator (PG) has the following characteristics:
PRR = 1MHz, t_r = 6ns, t_f = 6ns, t_w = 500ns,
V_p = 3V_{p-p}, Z₀ = 50Ω.
(2) C_L includes probe and jig capacitance.

4-BIT BISTABLE LATCH

TIMING REQUIREMENTS ($V_{CC}=5V$, $T_a=25^{\circ}C$, unless otherwise noted)


Symbol	Parameter	Test conditions	Limits			Unit
			Min	Typ	Max	
$t_{w(EH)}$	Enable input E high pulse width		20	7		ns
$t_{su(D)}$	Setup time 1D ~ 4D to E		20	12		ns
$t_h(D)$	Hold time 1D ~ 4D to E		8	5		ns

TIMING DIAGRAM (Reference level = 1.3V)




TYPE 14P4 14-PIN MOLDED PLASTIC DIL

Dimension in mm



TYPE 16P4 16-PIN MOLDED PLASTIC DIL

Dimension in mm



TYPE 20P4 20-PIN MOLDED PLASTIC DIL

Dimension in mm

