



Part Number: 75367-0015

Image not available

Status: Contact Molex
Series: 75367
Category: Backplane Connectors
Overview: GbX® Backplane Connector System

Series image - Reference only

Mates With Part(s):
 GbX® Backplane Connector Open Header
[75235](#) [75237](#)

Use With:
 Daughtercard Modules

Part Detail

General

Status	Contact Molex
Category	Backplane Connectors
Series	75367
Application	Daughtercard
Application Tooling Documents	TM-622022099
Comments	Daughtercard Module, Guidance
Component Type	Guide
Overview	GbX® Backplane Connector System
Product Name	GbX®
Style	N/A

Physical

Breakaway	No
Circuits (Loaded)	0
Color - Resin	Gray (Dark)
Durability (mating cycles max)	250
First Mate / Last Break	No
Guide to Mating Part	No
Keying to Mating Part	None
Material - Plating Mating	Gold
Material - Resin	High Temperature Thermoplastic
Number of Columns	N/A
Number of Pairs	5
Number of Rows	0
Orientation	Right Angle
PC Tail Length	2.50mm
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Tube
Pitch - Mating Interface	1.85mm
Pitch - Termination Interface	1.85mm
Polarized to PCB	Yes
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-55°C to +105°C

Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	1A
Data Rate	N/A
Voltage - Maximum	120V AC (RMS)/DC

Material Info

UPC	822348312528
-----	--------------

Reference - Drawing Numbers

Sales Drawing	SD-75367-001
---------------	--------------

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application
Tooling
[Check our list of old tooling that used to be
available for this part](#)