

8-bit compatible shift / store register

BU4094BC / BU4094BCF / BU4094BCFV


The BU4094BC, BU4094BCF, and BU4094BCFV are shift / store registers, each consisting of an 8-bit register and an 8-bit latch.

As the data in the shift register can be latched by an asynchronous strobe input, it is possible to hold the output in the data transfer mode.


The tri-state parallel output can be connected directly with an 8-bit bus line.

These registers are suitable for in-line / parallel data conversion, data receivers and other similar applications.

●Logic circuit diagram



●Block diagram



●Truth table

CLOCK	OUTPUT ENABLE	STROBE	SERIAL IN	Parallel output		Serial output	
				Q ₁	Q _n	Q _s	Q' _s
	H	H	L	L	Q _{n-1}	Q ₇	NC
	H	H	H	H	Q _{n-1}	Q ₇	NC
	H	L	X	NC	NC	Q ₇	NC
	L	X	X	Z	Z	Q ₇	NC
	H	X	X	NC	NC	NC	Q _s
	L	X	X	Z	Z	NC	Q _s

NC: No Change Z: High Impedance X: Irrelevant

●Absolute maximum ratings (Ta = 25°C)

Parameter	Symbol	Limits	Unit
Power supply voltage	V _{DD}	− 0.5 ~ + 20	V
Power dissipation	P _d	1000 (DIP), 500 (SOP) 400 (SSOP)	mW
Operating temperature	T _{opr}	− 40 ~ + 85	°C
Storage temperature	T _{stg}	− 55 ~ + 150	°C
Input voltage	V _{IN}	− 0.5 ~ V _{DD} + 0.5	V

●Electrical characteristics

DC characteristics (unless otherwise noted, V_{SS} = 0V, Ta = 25°C)

Parameter	Symbol	Min.	Typ.	Max.	Unit	V _{DD} (V)	Conditions
Input high level voltage	V _{IH}	3.5	—	—	V	5	—
		7.0	—	—		10	
		11.0	—	—		15	
Input low level voltage	V _{IL}	—	—	1.5	V	5	—
		—	—	3.0		10	
		—	—	4.0		15	
Input high level current	I _{IH}	—	—	0.3	μA	15	V _{IH} = 15V
Input low level current	I _{IL}	—	—	− 0.3	μA	15	V _{IL} = 0V
Output high level voltage	V _{OH}	4.95	—	—	V	5	I _O = 0mA
		9.95	—	—		10	
		14.95	—	—		15	
Output low level voltage	V _{OL}	—	—	0.05	V	5	I _O = 0mA
		—	—	0.05		10	
		—	—	0.05		15	
Output high level current	I _{OH}	− 0.44	—	—	mA	5	V _{OH} = 4.6V
		− 1.1	—	—		10	V _{OH} = 9.5V
		− 3.0	—	—		15	V _{OH} = 13.5V
Output low level current	I _{OL}	0.44	—	—	mA	5	V _{OL} = 0.4V
		1.1	—	—		10	V _{OL} = 0.5V
		3.0	—	—		15	V _{OL} = 1.5V
Output high level disable current	I _{DH}	—	—	1.0	μA	15	V _{OUT} = 15V
Output low level disable current	I _{DL}	—	—	− 1.0	μA	15	V _{OUT} = 0V
Static current dissipation	I _{DD}	—	—	20	μA	5	V _I = V _{DD} , or GND
		—	—	40		10	
		—	—	80		15	

Switching characteristics (unless otherwise noted, $V_{SS} = 0V$, $T_a = 25^\circ C$, $C_L = 50pF$)

Parameter	Symbol	Min.	Typ.	Max.	Unit	V _{DD} (V)	Conditions	Measurement circuit
Output rise time	t _{RLH}	—	100	—	ns	5	—	Fig.1
		—	50	—	ns	10		
		—	40	—	ns	15		
Output fall time	t _{RHL}	—	100	—	ns	5	—	Fig.1
		—	50	—	ns	10		
		—	40	—	ns	15		
Propagation delay time, CLOCK to Qs	t _{PLH} t _{PHL}	—	350	600	ns	5	—	Fig.1
		—	125	250	ns	10		
		—	95	190	ns	15		
Propagation delay time, CLOCK to Qs	t _{PLH} t _{PHL}	—	230	460	ns	5	—	Fig.1
		—	110	220	ns	10		
		—	75	150	ns	15		
Propagation delay time, CLOCK to Qn	t _{PLH} t _{PHL}	—	420	840	ns	5	—	Fig.1
		—	195	390	ns	10		
		—	135	270	ns	15		
Propagation delay time, STROBE to Qn	t _{PLH} t _{PHL}	—	290	580	ns	5	—	Fig.1
		—	145	290	ns	10		
		—	100	200	ns	15		
3-state propagation delay time, Output Enable to Qn	t _{PHZ} t _{PZH}	—	140	280	ns	5	R _L = 1k Ω	Fig.2
		—	75	150	ns	10		
		—	55	110	ns	15		
3-state propagation delay time, Output Enable to Qn	t _{PLZ} t _{PZL}	—	140	280	ns	5	R _L = 1k Ω	Fig.2
		—	75	150	ns	10		
		—	55	110	ns	15		
Minimum setup time, DATA to CLOCK	t _{su}	—	20	125	ns	5	—	Fig.1
		—	8	55	ns	10		
		—	6	35	ns	15		
Minimum hold time, CLOCK to DATA	t _h	—	10	40	ns	5	—	Fig.1
		—	10	20	ns	10		
		—	5	15	ns	15		
Minimum clock pulse width	t _w	—	100	200	ns	5	—	Fig.1
		—	50	100	ns	10		
		—	40	80	ns	15		
Maximum clock rise time and fall time	t _r (CL) t _f (CL)	NO Limit			μ s	5	—	Fig.1
					μ s	10		
					μ s	15		
Maximum clock frequency	f _{CL}	1.25	5	—	MHz	5	—	Fig.1
		2.5	10	—	MHz	10		
		3.0	12.5	—	MHz	15		
Minimum strobe pulse width	t _{WH}	—	100	200	ns	5	—	Fig.1
		—	40	80	ns	10		
		—	35	70	ns	15		
Input capacitance	C _{IN}	—	5	—	pF	—	—	—

● Measurement circuits




Fig. 1 Switching waveform

Fig. 2 3-state delay time




Fig. 3 Switching time test waveform

● Electrical characteristic curve





Fig. 4 Power dissipation vs. ambient temperature


● External dimensions (Units: mm)

BU4094BC




DIP16

BU4094BCF



SOP16

BU4094BCFV



SSOP-B16

Notes

- No technical content pages of this document may be reproduced in any form or transmitted by any means without prior permission of ROHM CO.,LTD.
- The contents described herein are subject to change without notice. The specifications for the product described in this document are for reference only. Upon actual use, therefore, please request that specifications to be separately delivered.
- Application circuit diagrams and circuit constants contained herein are shown as examples of standard use and operation. Please pay careful attention to the peripheral conditions when designing circuits and deciding upon circuit constants in the set.
- Any data, including, but not limited to application circuit diagrams information, described herein are intended only as illustrations of such devices and not as the specifications for such devices. ROHM CO.,LTD. disclaims any warranty that any use of such devices shall be free from infringement of any third party's intellectual property rights or other proprietary rights, and further, assumes no liability of whatsoever nature in the event of any such infringement, or arising from or connected with or related to the use of such devices.
- Upon the sale of any such devices, other than for buyer's right to use such devices itself, resell or otherwise dispose of the same, no express or implied right or license to practice or commercially exploit any intellectual property rights or other proprietary rights owned or controlled by
- ROHM CO., LTD. is granted to any such buyer.
- Products listed in this document use silicon as a basic material.
Products listed in this document are no antiradiation design.

The products listed in this document are designed to be used with ordinary electronic equipment or devices (such as audio visual equipment, office-automation equipment, communications devices, electrical appliances and electronic toys).

Should you intend to use these products with equipment or devices which require an extremely high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), please be sure to consult with our sales representative in advance.

About Export Control Order in Japan

Products described herein are the objects of controlled goods in Annex 1 (Item 16) of Export Trade Control Order in Japan.

In case of export from Japan, please confirm if it applies to "objective" criteria or an "informed" (by MITI clause) on the basis of "catch all controls for Non-Proliferation of Weapons of Mass Destruction.