


FULLY SEALABLE HEIDI-OSL SERIES FOR OSRAM OSLOM SSL/SX LEDS



OSRAM
www.osram.com



- Lens material optical grade PMMA with high UV and temperature resistance (105°C/220°F)
- High optical efficiency, up to 90%
- No lens holder. Fastening to heat sink with a PU foam adhesive tape of automotive grade
- We advise customer to ensure the suitability and sufficiency of the bond in the end product. For example, mechanical stress, vibration and holes on the surface of the circuit board weaken the strength of the tape.
- Please check fastening details from this link:
(http://www.ledil.com/datasheets/DataSheet_TAPE.pdf)
- Lens foot can be potted with resin without losses in optical efficiency (**fully sealed construction** of luminaire possible)
- Diameter 21.6 mm

LENS TYPES


NAME	ORDERING CODE	FWHM Angle
HEIDI diffuser	CA11264_Heidi-D-OSL	±3.5°
HEIDI medium	CA11265_Heidi-M-OSL	±14°
HEIDI oval	CA11266_Heidi-O-OSL	±26°, ±5°
Heidi oval 90°	CA11267_Heidi-O-90-OSL	±26°, ±5°
Heidi wide	CA11268_Heidi-W-OSL	Coming soon

NAME	ORDERING CODE	FWHM Angle
HEIDI diffuser	CA11264_Heidi-D-OSL-SX	To be measured shortly
HEIDI medium	CA11265_Heidi-M-OSL-SX	To be measured shortly
HEIDI oval	CA11266_Heidi-O-OSL-SX	To be measured shortly
Heidi oval 90°	CA11267_Heidi-O-90-OSL-SX	To be measured shortly
Heidi wide	CA11268_Heidi-W-OSL-SX	To be measured shortly

© Ledil Oy – Subject to change without prior notice



MEASUREMENTS

Relative Intensity of CA11264_Heidi-D-OSL




© Ledil Oy – Subject to change without prior notice

Relative Intensity of CA11265_Heidi-M-OSL



© Ledil Oy – Subject to change without prior notice

Relative Intensity of CA11266_Heidi-O-OSL




© Ledil Oy – Subject to change without prior notice

Ledil Oy
Tehdaskatu 13
FIN-24100 SALO, Finland

www.ledil.com
email: ledil@ledil.com
FAX: +358-2-733 8001

2011-03-08

DRAWINGS



© Ledil Oy – Subject to change without prior notice