





TABLE 1					
ITEM NO.	PART NUMBER	DESCRIPTION	MATERIAL TEMPERATURE RATING	CABLE LENGTH	UNIT QUANTITY
1	PSL-MLDH-X (ASSY)	MULTIPLE LOCKOUT DEVICE; STAINLESS STEEL WITH PLASTIC PIECE	185° F (85° C)	NA	1
2	PSL-MLDC	VINYL COATED GALVANIZED STEEL CABLE WITH LOOPHOLE	176° F (80° C)	6.0' (1.8M)	1
3	PSL-MLDCT	NYLON COATED GALVANIZED STEEL CABLE WITH LOOPHOLE	230° F (110° C)	6.0' (1.8M)	1
1, 2	PSL-MLD	MULTIPLE LOCKOUT DEVICE; INCLUDES LOCKOUT HASP AND VINYL COATED GALVANIZED STEEL CABLE WITH LOOPHOLE	185° F (85° C) DEVICE, 176° F (80° C) CABLE	6.0' (1.8M)	1 OF EACH
1, 3	PSL-MLDT	MULTIPLE LOCKOUT DEVICE; INCLUDES LOCKOUT HASP AND NYLON COATED GALVANIZED STEEL CABLE WITH LOOPHOLE	185° F (85° C) DEVICE, 230° F (110° C) CABLE	6.0' (1.8M)	1 OF EACH
4	PSL-MLDC200	VINYL COATED GALVANIZED STEEL CABLE WITHOUT LOOPHOLE	176° F (80° C)	200' (61M)	1
5	PSL-MLDC200T	NYLON COATED GALVANIZED STEEL CABLE WITHOUT LOOPHOLE	230° F (110° C)	200' (61M)	1

1 OPERATING TEMPERATURE AT LOW END IS -23° C.



CAD FILENAME/LAYERS		100619ZY_DC_C10391/02C	
PANDUIT		CORP. TINLEY PARK, ILLINOIS	
CUSTOMER DRAWING PSL-MLD		MULTI-PURPOSE LOCKOUT	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
(.X) ± .12 (.XX) ± .062		(.XXX) ± .020 ANGLES ±	
1	7/8/09	RVU	COMBINE MULTIPLE PARTS ON ONE DWG. REVISED TABLE 1 & ADD LOW END TEMP. NOTE.
0	2/2/06	RVU	DRAWING RELEASE.
REV	DATE	BY	CHK
DESCRIPTION		ECN	R
CUST		SUP	
DRAWN BY		MAT'L	
RVU		SEE TABLE 1.	
DATE		SCALE	
2/2/06		NTS	
CHK'D		DRAWING NO.	
		C10391	
		DWG SIZE	
		A	