

DK/EK-Series




The DK/EK-Series toggle switches are quick-make and quick-break type switches, suitable for high amperage AC/DC motor control. These heavy-duty switches are supplied with plated brass toggles and bushings in a phenolic base.

Specifications

- Certifications*: UL, CSA
- Dielectric Strength: 1,000 V (minimum)
- Insulation Resistance: 100 Megohms (minimum)
- Base Material: Phenolic
- Actuator Material: Brass/Nickel Plate
- Bezel Material: Brass/Nickel Plate

* Due to ongoing technological advances, consult factory for certification specifics.

Dimensional Specifications: in. [mm]



DK		28	4	-	73
SERIES/CIRCUIT		RATING	TERMINATION	TOGGLE STYLE	
DA ON-OFF SINGLE POLE		28 8A 250V	4 SCREW TERMINAL	TOGGLE BUSHING	SUFFIX
DK ON-OFF DOUBLE POLE		16A 125V		LENGTH LENGTH	NO.
		1HP 125-250V		BALL	.500 .343 32
				BAT	.687 .343 72
					.687 .465 73

EK		20	4	-	73
SERIES/CIRCUIT		RATING	TERMINATION	TOGGLE STYLE	
EA ON-OFF SINGLE POLE		20 10A 250V	4 SCREW TERMINAL	TOGGLE BUSHING	SUFFIX
EK ON-OFF DOUBLE POLE		20A 125V		LENGTH LENGTH	NO.
		1 1/2HP 125-250V		BALL	.500 .343 32
				BAT	.687 .343 72
					.687 .465 73

NOTES:
Shading indicates standard configurations.