

## Low Pass Filter

### EPB5016G



- Optimized for Broadcom BCM 6010 •

- Robust construction allows for IR/VP processes •


- Temperature Range -40°C to +85°C •

#### Electrical Parameters @ 25°C


Cut-off Frequency (MHz ± 1)	Insertion Loss (dB Max.)	Return Loss (dB Min.)	Attenuation (dB Min.)			Group Delay (μs Max.)
	10 KHz -8 MHz	10 KHz -8 MHz	@ 12 MHz	@ 13 MHz	@ 14-50 MHz	10 KHz -8 MHz
10	-1	-10	-25	-40	-45	200

- Characteristic Filter Impedance : 100 Ω •

#### Schematic



#### Package



#### Dimensions

Dim.	(Inches)			(Millimeters)		
	Min.	Max.	Nom.	Min.	Max.	Nom.
A	.870	.890	.880	22.10	22.61	22.35
B	.380	.400	.390	9.65	10.16	9.91
C	.223	.243	.233	5.66	6.17	5.92
D	---	---	.700	---	---	17.78
E	.003	.015	---	.254	.381	---
F	---	---	.100	---	---	2.54
G	.500	.520	.510	12.7	13.21	12.95
H	.016	.022	.019	.406	.559	.483
I	.008	.012	.010	.203	.305	.254
J	---	---	.140	---	---	3.56
K	0°	8°	---	0°	8°	---
L	.025	.045	.035	.635	1.14	.889
M	---	---	.030	---	---	.762
N	---	---	.100	---	---	2.54
P	---	---	.092	---	---	2.34
Q	---	---	.560	---	---	14.22