

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOC

DIST

AD

39

REV

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1

9

.300

6

.394

14

10

8-104078-4

1.650

33

1.744

68

10

8-104078-3

1.750

35

1.844

72

10

8-104078-2

.350

7

.444

16

10

8-104078-1

.800

16

.894

34

10

8-104078-0

.550

11

.644

24

10

7-104078-9

2.450

49

2.544

100

10

7-104078-8

1.950

39

2.044

80

10

7-104078-7

1.450

29

1.544

60

10

7-104078-6

1.200

24

1.294

50

10

7-104078-5

.700

14

.794

30

10

7-104078-4

.200

4

.294

10

7-104078-3

.950

19

1.044

40

7-104078-2

.450

9

.544

20

10

7-104078-1

7

.300

6

.394

14

10

6-104078-4

1.650

33

1.744

68

10

6-104078-3

1.750

35

1.844

72

11

6-104078-2

.350

7

.444

16

11

6-104078-1

.800

16

.894

34

6-104078-0

.550

11

.644

24

5-104078-9

2.450

49

2.544

100

5-104078-8

1.950

39

2.044

80

5-104078-7

1.450

29

1.544

60

5-104078-6

1.200

24

1.294

50

5-104078-5

.700

14

.794

30

5-104078-4

.200

4

.294

10

5-104078-3

.950

19

1.044

40

5-104078-2

.450

9

.544

20

5-104078-1

FINISH

C

B

A

NO OF POS

PART NUMBER

8

.300

6

.394

14

10

3-104078-4

1.650

33

1.744

68

10

3-104078-3

1.750

35

1.844

72

10

3-104078-2

.350

7

.444

16

10

3-104078-1

.800

16

.894

34

10

3-104078-0

.550

11

.644

24

10

2-104078-9

2.450

49

2.544

100

10

2-104078-8

1.950

39

2.044

80

10

2-104078-7

1.450

29

1.544

60

10

2-104078-6

1.200

24

1.294

50

10

2-104078-5

.700

14

.794

30

2-104078-4

.200

4

.294

10

10

2-104078-3

.950

19

1.044

40

10

2-104078-2

.450

9

.544

20

10

2-104078-1

1

.300

6

.394

14

10

1-104078-4

1.650

33

1.744

68

1-104078-3

1.750

35

1.844

72

12

1-104078-2

.350

7

.444

16

12

1-104078-1

.800

16

.894

34

1-104078-0

.550

11

.644

24

104078-9

2.450

49

2.544

100

104078-8

1.950

39

2.044

80

104078-7

1.450

29

1.544

60

104078-6

1.200

24

1.294

50

104078-5

.700

14

.794

30

104078-4

.200

4

.294

10

104078-3

.950

19

1.044

40

104078-2

.450

9

.544

20

104078-1

FINISH

C

B

A

NO OF POS

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
D. CLOUSER
CHK
T. KOCHER
APVD

1-15-87

1-15-87

TE Connectivity

DIMENSIONS:
INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0. PLC ± .
1. PLC ± .
2. PLC ± .
3. PLC ± .005
4. PLC ± .
ANGLES ± . ± .

PRODUCT SPEC
108-1093

APPLICATION SPEC
114-25031

WEIGHT
—

CUSTOMER DRAWING

NAME
RECEPTACLE ASSEMBLY,VERTICAL,
AMPMODU System 50

SIZE
A1

CAGE CODE
00779

DRAWING NO
104078

RESTRICTED TO
—

SCALE
4:1

SHEET
2

OF
2

REV
V

4805 (3/11)