



Features

- Formerly a JENSEN+DEVICES product
- Fast switching rate
- High energy, low loss capability
- Wide operating temperature range
- Long service life
- High insulation resistance
- RoHS compliant*

Applications

- Igniters for architectural and automotive Xenon discharge lamps
- Electronic igniters for gas heating and gas domestic appliances, e.g., cookers
- Ignition of ultra-high pressure gas discharge lamps for data and video projectors

Sparcube™ Switching Spark Gap ST-0620 Series

Description

Bourns® Sparcube™ Switching Spark Gap Series is a range of switching spark gaps designed specifically for voltage controlled switching of capacitive discharge circuits where a high energy, low loss, fast rate of switching is required. This series is ideally suited for applications where a capacitive discharge is utilized with a transformer to obtain pulses of very high voltage levels in the order of several thousand volts.

Characteristics

Initial Values:

Static Breakdown Voltage @ 800 V/s ¹

First Ignition Values < 750 V

Following Ignition Values 620 V ±12 %

Electrical Life:

Minimum Number of Switching Cycles 2x10⁵

Peak Current (Approx.) 750 A

Maximum Switching Frequency 200 Hz

Breakdown Characteristics @ 750 V Limit

First Ignition Values ≤ 750 V

Delay Time < 90 ms

Following Ignition Values 620 V ±15 %

General Data:

Breakdown Time < 50 ns

Insulation Resistance @ 100 Vdc > 100 megohms

Share of Early Ignition Values (< 527 V) < 1 %

Capacitance < 1 pF

Operating Temperature Range ² -40 °C to +160 °C

Storage Temperature Range -65 °C to +125 °C

Weight (Approx.) 2.3 g

Testing 100 %

Robustness of Terminations IEC 60068-2-21 ³


Notes:

¹ At delivery AQL 0.65 Level II, DIN ISO 2859.

² Distribution of switchings: maximum 20 % above +125 °C and 20 % below +20°C.

³ Test Ua1 (tensile), Ua2 (thrust), Ub (bending) and Uc (torsion).

Basic Application Circuit



BOURNS®

Asia-Pacific:

Tel: +886-2 2562-4117

Fax: +886-2 2562-4116

EMEA:

Tel: +36 88 520 390

Fax: +36 88 520 211

The Americas:

Tel: +1-951 781-5500

Fax: +1-951 781-5700

www.bourns.com

*RoHS Directive 2002/95/EC Jan. 27, 2003 including annex and RoHS Recast 2011/65/EU June 8, 2011.

Specifications are subject to change without notice.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time.


Users should verify actual device performance in their specific applications.

Sparctube™ Switching Spark Gap ST-0620 Series


BOURNS®

Product Dimensions


ST-0620-BLx



ST-0620-BCx



ST-0620-BBx



How to Order

ST - 0620 - B x x - STD


Series Designator
 Switching Voltage 0620 = 620 V
 Tolerance B = 12 %
 Lead Shape B = Bent Leads, C = No Leads*, L = Straight Leads
 Packaging B = Bulk, T = Tape & Reel*
 Standard or Modified Product Indicator STD = Standard

*Leadless version available in bulk packaging only.

Typical Part Marking

B ST 0620 wwyy "wwyy" = Week and year of production

Test Circuit



Uo750 V
 RSee Note
 C470 nF
 L0.5 μH
 DUTDevice Under Test
 UsBreakdown Voltages

NOTE: Uo and R are set to provide suitable conditions for different measurements.

Specifications are subject to change without notice.
 The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time.
 Users should verify actual device performance in their specific applications.

Sparctube™ Switching Spark Gap ST-0620 Series


BOURNS®

Packaging Specifications


Models ST-0620-BBB, ST-0620-BLB and ST-0620-BCB* ship standard bulk pack, 1,000 pcs./bag. The optional tape and reel packaging contains 1,000 pcs./reel for Model ST-0620-BLT; 500 pcs./reel for Model ST-0620-BBT.

* Available in bulk packaging only.

ST-0620-BLT



ST-0620-BBT



DIMENSIONS: $\frac{\text{MM}}{(\text{INCHES})}$

REV. 04/17/14

"Sparctube" is a registered trademark of Bourns, Inc. in China and the European Community, with a trademark registration application pending in the U.S.

Specifications are subject to change without notice.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time.

Users should verify actual device performance in their specific applications.