




+ TERMINALS & SPLICES

CRIMP WIRE PINS, TABS & FERRULES



✓ Active

TE CONNECTIVITY (TE)

B-106-7401CS100

Raychem | TERMINAL , Terminator

CC2631-000

TE Internal Number: CC2631-000

Not Yet Reviewed for EU RoHS

Not Yet Reviewed for EU ELV

Terminal Type Bullet

Wire Insulation Diameter (Max) 4 mm [.16 in]

Wire Insulation Diameter 1.4 – 4 mm [.06 – .157 in]

Heavy Duty No

Wire Size (AWG) 22 – 18

↓ PRODUCT DRAWING
English

DOCUMENTATION

Product Drawings

Duraseal Bullet Terminal

PDF

English

Product Specifications

Product Specification

Installation Procedure For Duraseal Splices And Terminals

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Barrel Type Closed Barrel

Insulated Yes

Support Style Insulation Support

Body Features

Plating Material Copper Alloy, Tin

Insulation Material Heat Shrinkable Nylon

Double Wire No

Insulation Sleeve Material Polyamide

Contact Features

Terminal Type Bullet

Termination Features

Bullet Terminal With

Bullet Diameter 4 mm [.157 in]

Dimensions

Wire Insulation Diameter (Max) 4 mm [.16 in]

Wire Insulation Diameter 1.4 – 4 mm [.06 – .157 in]

Wire Size (AWG) 22 – 18

Wire Size (mm²) .3 – .9

Wire Size (CMA) 509 – 1900

Barrel Inside Diameter 4 mm [.16 in]

Overall Length 33 mm [1.3 in]

Operation/Application

Heavy Duty No

Packaging Features

Packaging Method Bag

Packaging Quantity 100

Other

Barrel Color Red

PRODUCT COMPLIANCE



Statement of Compliance

[Statement of Compliance](#)

PDF
