







WIRING DIAGRAM					LOCKNUT LN-SS08					SPECIFICATIONS																																																									
										<table><tr><td>RATED OPERATING DISTANCE</td><td>2.0 mm = .079"</td></tr><tr><td>MOUNTING MODE</td><td>FLUSH</td></tr><tr><td>MIN. REPEAT ACCURACY</td><td>≤ 2%</td></tr><tr><td>TEMPERATURE DRIFT</td><td>≤ ± 10%</td></tr><tr><td>HYSTERESIS</td><td>3-15%</td></tr><tr><td>OPERATING TEMPERATURE</td><td>-25°C to +70°C (-13°F to +158°F)</td></tr><tr><td>RATED OPERATIONAL VOLTAGE</td><td>10-30 VDC</td></tr><tr><td>RESIDUAL RIPPLE</td><td>≤10%</td></tr><tr><td>RATED OPERATIONAL CURRENT (DC)</td><td>≤150 mA</td></tr><tr><td>NO-LOAD CURRENT</td><td>≤ 15 mA</td></tr><tr><td>RESIDUAL CURRENT</td><td>≤ 0.1 mA</td></tr><tr><td>RATED INSULATION VOLTAGE</td><td>≤ 0.5 kV</td></tr><tr><td>SHORT-CIRCUIT PROTECTED</td><td>YES</td></tr><tr><td>MAX VOLTAGE DROP</td><td>≤ 1.8 V</td></tr><tr><td>WIRE BREAKAGE PROTECTION</td><td>INCORPORATED</td></tr><tr><td>REVERSE POLARITY PROTECTION</td><td>INCORPORATED</td></tr><tr><td>OUTPUT FUNCTION</td><td>4-WIRE, CHANGE OVER, PNP</td></tr><tr><td>MAX. SWITCHING FREQUENCY</td><td>≤ 3.0 kHz</td></tr><tr><td>HOUSING MATERIAL</td><td>METAL, A4 1.4404 (AISI 316L)</td></tr><tr><td>ACTIVE FACE MATERIAL</td><td>PLASTIC, PA12-GF20</td></tr><tr><td>END CAP MATERIAL</td><td>PLASTIC, PP</td></tr><tr><td>CABLE</td><td>ø4.0, TPU</td></tr><tr><td>SHOCK RESISTANCE</td><td>30 g, 11 ms</td></tr><tr><td>VIBRATION RESISTANCE</td><td>55 Hz, 1 mm AMPLITUDE (IN ALL 3 PLANES)</td></tr><tr><td>DEGREE OF PROTECTION</td><td>IP67</td></tr><tr><td>SWITCHING STATUS INDICATION</td><td>LED: YELLOW</td></tr></table>					RATED OPERATING DISTANCE	2.0 mm = .079"	MOUNTING MODE	FLUSH	MIN. REPEAT ACCURACY	≤ 2%	TEMPERATURE DRIFT	≤ ± 10%	HYSTERESIS	3-15%	OPERATING TEMPERATURE	-25°C to +70°C (-13°F to +158°F)	RATED OPERATIONAL VOLTAGE	10-30 VDC	RESIDUAL RIPPLE	≤10%	RATED OPERATIONAL CURRENT (DC)	≤150 mA	NO-LOAD CURRENT	≤ 15 mA	RESIDUAL CURRENT	≤ 0.1 mA	RATED INSULATION VOLTAGE	≤ 0.5 kV	SHORT-CIRCUIT PROTECTED	YES	MAX VOLTAGE DROP	≤ 1.8 V	WIRE BREAKAGE PROTECTION	INCORPORATED	REVERSE POLARITY PROTECTION	INCORPORATED	OUTPUT FUNCTION	4-WIRE, CHANGE OVER, PNP	MAX. SWITCHING FREQUENCY	≤ 3.0 kHz	HOUSING MATERIAL	METAL, A4 1.4404 (AISI 316L)	ACTIVE FACE MATERIAL	PLASTIC, PA12-GF20	END CAP MATERIAL	PLASTIC, PP	CABLE	ø4.0, TPU	SHOCK RESISTANCE	30 g, 11 ms	VIBRATION RESISTANCE	55 Hz, 1 mm AMPLITUDE (IN ALL 3 PLANES)	DEGREE OF PROTECTION	IP67	SWITCHING STATUS INDICATION	LED: YELLOW	
RATED OPERATING DISTANCE	2.0 mm = .079"																																																																		
MOUNTING MODE	FLUSH																																																																		
MIN. REPEAT ACCURACY	≤ 2%																																																																		
TEMPERATURE DRIFT	≤ ± 10%																																																																		
HYSTERESIS	3-15%																																																																		
OPERATING TEMPERATURE	-25°C to +70°C (-13°F to +158°F)																																																																		
RATED OPERATIONAL VOLTAGE	10-30 VDC																																																																		
RESIDUAL RIPPLE	≤10%																																																																		
RATED OPERATIONAL CURRENT (DC)	≤150 mA																																																																		
NO-LOAD CURRENT	≤ 15 mA																																																																		
RESIDUAL CURRENT	≤ 0.1 mA																																																																		
RATED INSULATION VOLTAGE	≤ 0.5 kV																																																																		
SHORT-CIRCUIT PROTECTED	YES																																																																		
MAX VOLTAGE DROP	≤ 1.8 V																																																																		
WIRE BREAKAGE PROTECTION	INCORPORATED																																																																		
REVERSE POLARITY PROTECTION	INCORPORATED																																																																		
OUTPUT FUNCTION	4-WIRE, CHANGE OVER, PNP																																																																		
MAX. SWITCHING FREQUENCY	≤ 3.0 kHz																																																																		
HOUSING MATERIAL	METAL, A4 1.4404 (AISI 316L)																																																																		
ACTIVE FACE MATERIAL	PLASTIC, PA12-GF20																																																																		
END CAP MATERIAL	PLASTIC, PP																																																																		
CABLE	ø4.0, TPU																																																																		
SHOCK RESISTANCE	30 g, 11 ms																																																																		
VIBRATION RESISTANCE	55 Hz, 1 mm AMPLITUDE (IN ALL 3 PLANES)																																																																		
DEGREE OF PROTECTION	IP67																																																																		
SWITCHING STATUS INDICATION	LED: YELLOW																																																																		
																																																																			
SOURCE DRAWING - FOR REFERENCE ONLY																																																																			
<table><tr><th colspan="4">RELATED DOCUMENTS</th><th colspan="2">3RD ANGLE PROJECTION</th><th colspan="2">THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.</th><th colspan="2"><div>TURCK INC</div><div>High Technology Sensors and Automation Controls</div></th><th colspan="3">3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com</th></tr><tr><td>1.</td><td>2.</td><td>3.</td><td>4.</td><td colspan="2" rowspan="2"></td><td>DRFT</td><td>RWC</td><td>DATE</td><td>01/21/10</td><td colspan="3" rowspan="2">DESCRIPTION BI 2-EG08-VP6X-0.2M-RS 4.4T</td></tr><tr><td colspan="4">MATERIAL SEE SPECS</td><td>DSGN</td><td></td><td>SCALE</td><td>1=1.0</td></tr><tr><td colspan="4">FINISH SEE SPECS</td><td colspan="2" rowspan="2">ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY</td><td colspan="4">UNIT OF MEASUREMENT INCH [MILLIMETER]</td><td colspan="2">IDENTIFICATION NO. S1604680</td><td>REV C</td></tr><tr><td colspan="4"></td><td colspan="4">DO NOT SCALE THIS DRAWING</td><td colspan="2">FILE: S1604680</td><td>SHEET 1 OF 1</td></tr></table>					RELATED DOCUMENTS				3RD ANGLE PROJECTION		THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		<div>TURCK INC</div> <div>High Technology Sensors and Automation Controls</div>		3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com			1.	2.	3.	4.			DRFT	RWC	DATE	01/21/10	DESCRIPTION BI 2-EG08-VP6X-0.2M-RS 4.4T			MATERIAL SEE SPECS				DSGN		SCALE	1=1.0	FINISH SEE SPECS				ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		UNIT OF MEASUREMENT INCH [MILLIMETER]				IDENTIFICATION NO. S1604680		REV C					DO NOT SCALE THIS DRAWING				FILE: S1604680		SHEET 1 OF 1					
RELATED DOCUMENTS				3RD ANGLE PROJECTION		THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		<div>TURCK INC</div> <div>High Technology Sensors and Automation Controls</div>		3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com																																																									
1.	2.	3.	4.			DRFT	RWC	DATE	01/21/10	DESCRIPTION BI 2-EG08-VP6X-0.2M-RS 4.4T																																																									
MATERIAL SEE SPECS						DSGN		SCALE	1=1.0																																																										
FINISH SEE SPECS				ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		UNIT OF MEASUREMENT INCH [MILLIMETER]				IDENTIFICATION NO. S1604680		REV C																																																							
						DO NOT SCALE THIS DRAWING				FILE: S1604680		SHEET 1 OF 1																																																							
C	DRAWING PROCESSED AS PART OF ECO 33971			CBM	04/06/11	33971																																																													
REV	DESCRIPTION			BY	DATE	ECO NO.																																																													