

## Duplex Singlemode 8.3/125 Fiber Patch Cable (LC/LC), 5M (16-ft.)

MODEL NUMBER: **N370-05M**



### Description

Tripp Lite's 5-meter, single mode duplex fiber optic LC/LC patch cable is manufactured from 8.3/125 zipcord fiber. The cable has LC connectors on one end, LC connectors on the other, a PVC jacket, and is FDDI and OFNR rated. Duplex single mode fiber is most commonly used in LAN applications.

### Features

- Manufactured from 8.3/125 duplex (zipcord) fiber
- PVC jacket
- Length: 5-meter. Connectors: 2 LC and 2 LC connectors on each end
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)
- Color coded shrouds identify transmit and receive
- Fiber optic distributed data interface (FDDI) rated
- OFNR (riser rated)

## Specifications

General Info	
Product Group	NETWORK CABLES
OVERVIEW	
Clad Diameter	125 micron
Core Diameter	8.3 micron

### Highlights

- Premium PVC 8.3/125 micron singlemode patch cables
- Attenuation loss meets or exceeds the latest industry standards
- Twice the bandwidth throughput of multimode cable

### Applications

- Networking equipment that requires single mode fiber optic patch cables

### System Requirements

- Any fiber optic hardware or NIC card requiring singlemode duplex cable with LC/LCconnectors

### Package Includes

- 5-meter Duplex Single mode Fiber Patch Cable, LC/LC

Fiber Type	8.3/125
Number of Fibers	2
Intended Application	Computer Networking (Fiber)
Cable Type	SINGLEMODE 8.3/125 FIBER OPTIC
Model Type	LC/LC
<b>INPUT</b>	
Cable Length (m)	5
<b>UPC ASSIGNMENT</b>	
Unit Carton UPC#	037332099518
<b>PHYSICAL</b>	
Color	Yellow
Style	Fiber Optic
<b>CONNECTIONS</b>	
Connector A	LC
Connector B	LC
Number of Connectors	4
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.