

TLP160G

Triac Drive
Programmable Controllers
AC-Output Module
Solid State Relay

The TOSHIBA mini flat coupler TLP160G is a small outline coupler, suitable for surface mount assembly.
The TLP160G consists of a photo triac, optically coupled to a gallium arsenide infrared emitting diode.


- Peak off-state voltage: 400 V (min.)
- Trigger LED current: 10 mA (max.)
- On-state current: 70 mA (max.)
- Isolation voltage: 2500 Vrms (min.)
- UL recognized: UL1577, file No. E67349

Trigger LED Current

Classi- fication*	Trigger LED Current (mA)		Marking of Classification
	V _T =3V, T _a =25°C		
	Min.	Max.	
(IFT5)	—	5	T5
(IFT7)	—	7	T5, T7
Standard	—	10	T5, T7, blank


*Ex. (IFT5); TLP160G (IFT5)
(Note) Application type name for certification test, please use standard product type name, i.e.
TLP160G(IFT5): TLP160G

Unit in mm



Weight: 0.09 g

Pin Configurations



- 1. Anode
- 3. Cathode
- 4. Terminal 1
- 6. Terminal 2

Maximum Ratings (Ta = 25°C)

Characteristics			Symbol	Rating	Unit
LED	Forward current		I _F	50	mA
	Forward current derating (Ta ≥ 53°C)		ΔI _F / °C	−0.7	mA / °C
	Peak forward current (100μs pulse, 100 pps)		I _{FP}	1	A
	Reverse voltage		V _R	5	V
	Junction temperature		T _j	125	°C
Detector	Off- state output terminal voltage		V _{DRM}	400	V
	On-state RMS current	Ta=25°C	I _{T(RMS)}	70	mA
		Ta=70°C		40	
	On-state current derating (Ta ≥ 25°C)		ΔI _T / °C	−0.67	mA / °C
	Peak on-state current (100μs pulse, 120 pps)		I _{TP}	2	A
	Peak nonrepetitive surge current (PW=10ms, DC=10%)		I _{TSM}	1.2	A
	Junction temperature		T _j	115	°C
Storage temperature range			T _{stg}	−55~125	°C
Operating temperature range			T _{opr}	−40~100	°C
Lead soldering temperature (10s)			T _{sol}	260	°C
Isolation voltage (AC, 1 min., R.H. ≤ 60%) (Note)			BV _S	2500	Vrms

(Note) Device considered a two terminal device: Pins 1 and 3 shorted together and pins 4 and 6 shorted together.

Recommended Operating Conditions

Characteristics	Symbol	Min.	Typ.	Max.	Unit
Supply voltage	V_{AC}	—	—	120	Vac
Forward current	I_F	15	20	25	mA
Peak on-state current	I_{TP}	—	—	1	A
Operating temperature	T_{opr}	-25	—	85	°C


Individual Electrical Characteristics (Ta = 25°C)







Characteristics		Symbol	Test Condition	Min.	Typ.	Max.	Unit
LED	Forward voltage	V_F	$I_F=10\text{mA}$	1.0	1.15	1.3	V
	Reverse current	I_R	$V_R=5\text{V}$	—	—	10	μA
	Capacitance	C_T	$V=0, f=1\text{MHz}$	—	30	—	pF
Detector	Peak off-state current	I_{DRM}	$V_{\text{DRM}}=400\text{V}$	—	10	1000	nA
	Peak on-state voltage	V_{TM}	$I_{\text{TM}}=70\text{mA}$	—	1.7	2.8	V
	Holding current	I_H	—	—	0.6	—	mA
	Critical rate of rise of off-state voltage	dv/dt	$V_{\text{in}}=120\text{Vrms}, T_a=85^\circ\text{C}$ (Fig.1)	200	500	—	V / μs
	Critical rate of rise of commutating voltage	$dv/dt(c)$	$I_T=15\text{mA}, V_{\text{in}}=30\text{Vrms}$ (Fig.1)	—	0.2	—	V / μs






Coupled Electrical Characteristics (Ta = 25°C)

Characteristics	Symbol	Test Condition	Min.	Typ.	Max.	Unit
Trigger LED current	I_{FT}	$V_T=3\text{V}$	—	5	10	mA
Capacitance input to output	C_s	$V_S=0, f=1\text{MHz}$	—	0.8	—	pF
Isolation resistance	R_S	$V_S=500\text{V}, \text{R.H.} \leq 60\%$	1×10^{12}	10^{14}	—	Ω
Isolation voltage	BV_S	AC, 1 minute	2500	—	—	Vrms
		AC, 1 second, in oil	—	5000	—	
		DC, 1 minute, in oil	—	5000	—	Vdc
Turn-on time	t_{ON}	$V_D=6 \rightarrow 4\text{V}, R_L=100\Omega$ $I_F=\text{rated } I_{\text{FT}} \times 1.5$	—	30	100	μs

Fig.1 dv / dt Test Circuit







RESTRICTIONS ON PRODUCT USE

000707EAA

- TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such TOSHIBA products could cause loss of human life, bodily injury or damage to property.
In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the "Handling Guide for Semiconductor Devices," or "TOSHIBA Semiconductor Reliability Handbook" etc..
- The TOSHIBA products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These TOSHIBA products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc.. Unintended Usage of TOSHIBA products listed in this document shall be made at the customer's own risk.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA CORPORATION for any infringements of intellectual property or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any intellectual property or other rights of TOSHIBA CORPORATION or others.
- The information contained herein is subject to change without notice.