


REVISIONS		DOC. NO. SPC-F005 * Effective: 12/21/98 * DCP No: 680							
DCP #	REV	DESCRIPTION		DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1210	D	Renamed and Updated		JWM	12/18/01	DJC	12/28/01	DJC	12/28/01



NOTES:

1. MATERIAL:
CONTACT: BRASS BODY PER QQ-B-626D
WITH WRAP AROUND BERYLLIUM COPPER
SPRING PER QQ-C-533
BODY: NYLON 66 PER ASTM D4066
2. FINISH: SILVER
3. PANEL THICKNESS: UP TO .375" [9.05 MM].
4. FLAMMABILITY: UL94V-2
SELF-EXTINGUISHING
5. CONTINUOUS USE TEMPERATURE:
-40°F (-40°C) TO 185°F (85°C)
6. CURRENT RATING: 5 AMPS
7. BREAKDOWN VOLTAGE: 3500 VRMS MINIMUM
8. CONTACT RESISTANCE: .005 OHMS MAX.
9. CONTACT-TO-PANEL CAP.: 1 pF NOMINAL
10. FOR STANDARD TIP PLUG .080" [2 MM].
11. MACHINED CONTACT WITH TURRET TERMINAL.
12. INSTALLS BY PRESSING INTO MOUNTING
HOLE, NO MOUNTING HARDWARE REQUIRED.
13. CLOSED ENTRY BLOCKS ACCES OF PROBES
GREATER THAN .085" [2.16 MM].

PANEL AND MOUNTING HOLE LAYOUT

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION
AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE
BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE
INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



SPC TECHNOLOGY

Tolerances: Unless
Otherwise Specified:

$X = \pm .015$
 $XX = \pm .010$
 $XXX = \pm .005$