

HS5A - HS5M


5.0 AMPS. High Efficient Surface Mount Rectifiers

SMC/DO-214AB



Features

- ✧ Glass passivated junction chip.
- ✧ For surface mounted application
- ✧ Low forward voltage drop
- ✧ Low profile package
- ✧ Built-in stain relief, ideal for automatic placement
- ✧ Fast switching for high efficiency
- ✧ High temperature soldering:
260°C/10 seconds at terminals
- ✧ Plastic material used carries Underwriters
Laboratory Classification 94V0



Mechanical Data

- ✧ Cases: Molded plastic
- ✧ Terminals: Pure tin plated, lead free
- ✧ Polarity: Indicated by cathode band
- ✧ Packing: 16mm tape per EIA STD RS-481
- ✧ Weight: 0.21 gram

Dimensions in inches and (millimeters)

Maximum Ratings and Electrical Characteristics

Rating at 25 °C ambient temperature unless otherwise specified.

Single phase, half wave, 60 Hz, resistive or inductive load.

For capacitive load, derate current by 20%

Type Number	Symbol	HS 5A	HS 5B	HS 5D	HS 5F	HS 5G	HS 5J	HS 5K	HS 5M	Units
Maximum Recurrent Peak Reverse Voltage	V _{RRM}	50	100	200	300	400	600	800	1000	V
Maximum RMS Voltage	V _{RMS}	35	70	140	210	280	420	560	700	V
Maximum DC Blocking Voltage	V _{DC}	50	100	200	300	400	600	800	1000	V
Maximum Average Forward Rectified Current See Fig. 1	I _(AV)	5.0								A
Peak Forward Surge Current, 8.3 ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	I _{FSM}	150								A
Maximum Instantaneous Forward Voltage @ 5.0A	V _F	1.0				1.3	1.7			V
Maximum DC Reverse Current @ T _A =25 °C at Rated DC Blocking Voltage @ T _A =125 °C	I _R	10 250								uA uA
Maximum Reverse Recovery Time (Note 1)	T _{rr}	50					75			nS
Typical Junction Capacitance (Note 2)	C _j	80					50			pF
Maximum Thermal Resistance (Note 3)	R _{θJA}	60								°C/W
Operating Temperature Range	T _J	-55 to +150								°C
Storage Temperature Range	T _{STG}	-55 to +150								°C

- Notes:
1. Reverse Recovery Test Conditions: $I_F=0.5\text{A}$, $I_R=1.0\text{A}$, $I_{RR}=0.25\text{A}$
 2. Measured at 1 MHz and Applied $V_R=4.0\text{ Volts}$.
 3. Measured on P.C.Board with 0.6" x 0.6" (16mm x 16mm) Copper Pad Area.

RATINGS AND CHARACTERISTIC CURVES (HS5A THRU HS5M)

FIG.1- MAXIMUM FORWARD CURRENT DERATING CURVE




FIG.3- MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT




FIG.4- TYPICAL JUNCTION CAPACITANCE




FIG.2- TYPICAL REVERSE CHARACTERISTICS




FIG.5- TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS






FIG.6- REVERSE RECOVERY TIME CHARACTERISTIC AND TEST CIRCUIT DIAGRAM



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Taiwan Semiconductor:](#)

[HS5A](#) [HS5B](#) [HS5D](#) [HS5F](#) [HS5G](#) [HS5J](#) [HS5K](#) [HS5M](#)