

LOC	DIST	REVISIONS					
P	LTR	DESCRIPTION				DATE	APVD
		B				16/05/07	FWK

NOTES:

1. ELECTRICAL DATA:

CONTACT RESISTANCE: 10 mOhm MAX

INSULATION RESISTANCE: 100 MOhm MIN at 500VDC

CURRENT RATING: 5 AMPS

BREAKDOWN VOLTAGE: 500 VAC MIN PER MINUTE
2. ENVIRONMENTAL:

OPERATING TEMPERATURE: −25°C TO +90°C


SEALING REQUIREMENTS: IP67
3. PROD SPEC:

108−3641
4. PACKAGING:


107−3334
5. FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE
6. ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED

ITEM	DESCRIPTION	MATERIAL	FINISH/COLOUR	QTY
1	SCREW NUT	ZINC DIE CAST	2.5µm NICKEL PLATED	1
2	CONNECTOR BODY	POLYURETHANE	BLACK	1
3	SOCKET CONTACT	BRASS	0.15µm GOLD PLATED OVER NICKEL	4
4	4 CORE CABLE (CORES 0.34 mm ²)	PU JACKET	BLACK	1
5	'O' RING	VITON	GREEN	1

PIN ASSIGNMENTS
FRONT VIEW




4	BLACK
3	BLUE
2	WHITE
1	BROWN
PIN	WIRE COLOUR



10000	500 mm	M12 RIGHT ANGLED FEMALE CONNECTOR 10.0m CABLE	1838257−5
7000	350 mm	M12 RIGHT ANGLED FEMALE CONNECTOR 7.0m CABLE	1838257−4
5000	250 mm	M12 RIGHT ANGLED FEMALE CONNECTOR 5.0m CABLE	1838257−3
3000	150 mm	M12 RIGHT ANGLED FEMALE CONNECTOR 3.0m CABLE	1838257−2
2000	100 mm	M12 RIGHT ANGLED FEMALE CONNECTOR 2.0m CABLE	1838257−1
DIM A	TOL 'B'	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± −

1 PLC ± −

2 PLC ± −

3 PLC ± −

4 PLC ± −

ANGLES ± −

FINISH −

DWN H M RAGHAVENDRA

CHK F.WHEELER−KING

APVD F.WHEELER−KING

PRODUCT SPEC −

APPLICATION SPEC −

WEIGHT −

 Tyco Electronics Corporation
Bideford, UK, EX39 4HE

NAME
M12 RIGHT ANGLED FEMALE CONNECTOR
4 POSITION, PU CABLE

SIZE A3

CAGE CODE 00779

DRAWING NO C=1838257

RESTRICTED TO −

CUSTOMER DRAWING

SCALE NTS

SHEET 1 OF 1

REV B

AMP 1470−19 REV 31MAR2000