



For stripping and assembly instnuctions see Drawing Number: VAIF1301

Electrical Characteristics	
Nominal Impedance:	Non Constant
Frequency Range:	DC to 2 GHz
VSWR:	1.35:1 maximum
Operating Voltage (rms):	250 V maximum at sea level
Mechanical Characteristics	
Mating Cycles:	200 cycles minimum
Environmental Characteristics	
Temperature Range:	-55 °C to +85 °C

	PART	DESCRIPTION
1	Body	Brass, nickel plated



Connectivity Solutions
7-13 Russel Way,
Widford Industrial Estate,
Chelmsford,Essex,
CM1 3AA, UK.
Tel: +44 (0) 1245 359515
Fax: +44 (0) 1245 358938

SCALE: Not To Scale	DRAWN BY:	S Nash	TITLE: F Twist-On Plug for RG59	PART NUMBER:	
DIMENSIONS: mm	CHECKED BY:	P Couzens		TOF59	
TOLERANCES: ± 0.2mm unless otherwise stated	APPROVED BY:	P Couzens		PAGE: 1 of 1	
	DATE:	12 Sep 02			