


Features

- LO = 2.5 - 10.5 GHz
- RF = 4.5 - 8.5 GHz
- IF = DC - 2.0 GHz
- Low Drive: 20 dBm (nominal)
- High OIP3: 24 dBm

Description

The M76H is a double balanced mixer, designed for use in military, commercial and test equipment applications. The design utilizes Schottky ring quad diodes and broadband soft dielectric and ferrite baluns to attain excellent performance. This mixer can also be used as a phase detector and/or bi-phase modulator since the IF port is DC coupled to the diodes. The use of high temperature solder and welded assembly processes used internally makes it ideal for use in manual, semi-automated assembly. Environmental screening available to MIL-STD-883, MIL-STD-202, or MIL-DTL-28837, consult factory.



Electrical Specifications: $Z_0 = 50 \Omega$ $Lo = +20$ dBm (downconverter application only)

Parameter	Test Conditions	Units	Typical	Guaranteed	
				+25°C	-54° to +85°C
SSB Conversion Loss (max.) & SSB Noise Figure (max.)	RF = 4.5 - 8.0 GHz, LO = 2.5 - 10.0 GHz, IF = 0.03 - 2.0 GHz RF = 8.0 - 8.5 GHz, LO = 6.5 - 9.5 GHz, IF = 0.03 - 1.5 GHz RF = 8.0 - 8.5 GHz, LO = 6.0 - 10.5 GHz, IF = 0.03 - 2.0 GHz	dB	5.5 6.5 8.0	7.0 8.0 9.5	7.5 8.3 9.8
Isolation, LO to RF (min.)	LO = 2.5 - 10.5 GHz	dB	35	22	21
Isolation, LO to IF (min.)	LO = 2.5 - 6.5 GHz LO = 6.5 - 10.5 GHz	dB	22 30	15 20	14 19
1 dB Conversion Comp.	LO = 20 dBm	dBm	15	—	—
Input IP3	RF1 = 6.12 GHz @ 0 dBm, RF2 = 6.18 GHz @ 0 dBm, LO = 7.2 GHz @ = 20 dBm	dBm	24	—	—

Ordering Information


Part Number	Package
M76H	Minpac
M76HC	SMA Connectorized

Absolute Maximum Ratings


Parameter	Absolute Maximum
Peak Input Power	25 dBm @ +25°C 23 dBm @ +100°C
Peak Input Current	100 mA DC
Operating Temperature	-54°C to +100°C
Storage Temperature	-65°C to +100°C

Typical Performance Curves


Conversion Loss vs. LO Drive Power
 RF = 5 GHz, IF = 1 GHz, LO > RF




Conversion Loss vs. Frequency (Up Conversion)
 RF = 7 GHz, Input to R-Port, LO Power = 20 dBm




Conversion Loss vs. Frequency (Down Conversion)
 IF = 1 GHz, Output @ I-Port, LO Power = 20 dBm




Conversion Loss vs. Frequency (Up Conversion)
 IF = 1 GHz, Input to I-Port, LO Power = 20 dBm



Conversion Loss vs. Frequency (Down Conversion)
 IF = 2 GHz, Output @ I-Port, LO Power = 20 dBm




Isolation vs. Frequency
 LO Power = 20 dBm




Typical Performance Curves


L-Port VSWR (LO = 20 dBm)




I-Port VSWR (LO = 7.2 GHz @ 20 dBm)




R-Port VSWR (LO = 7.2 GHz @ 20 dBm)



Outline Drawing: Minpac*



Outline Drawing: SMA Connectorized*



*Dimensions are inches (millimeters) ± 0.015 (0.38) unless otherwise specified.

MACOM Technology Solutions Inc. All rights reserved.

Information in this document is provided in connection with MACOM Technology Solutions Inc ("MACOM") products. These materials are provided by MACOM as a service to its customers and may be used for informational purposes only. Except as provided in MACOM's Terms and Conditions of Sale for such products or in any separate agreement related to this document, MACOM assumes no liability whatsoever. MACOM assumes no responsibility for errors or omissions in these materials. MACOM may make changes to specifications and product descriptions at any time, without notice. MACOM makes no commitment to update the information and shall have no responsibility whatsoever for conflicts or incompatibilities arising from future changes to its specifications and product descriptions. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document.

THESE MATERIALS ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, RELATING TO SALE AND/OR USE OF MACOM PRODUCTS INCLUDING LIABILITY OR WARRANTIES RELATING TO FITNESS FOR A PARTICULAR PURPOSE, CONSEQUENTIAL OR INCIDENTAL DAMAGES, MERCHANTABILITY, OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT. MACOM FURTHER DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. MACOM SHALL NOT BE LIABLE FOR ANY SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS, WHICH MAY RESULT FROM THE USE OF THESE MATERIALS.

MACOM products are not intended for use in medical, lifesaving or life sustaining applications. MACOM customers using or selling MACOM products for use in such applications do so at their own risk and agree to fully indemnify MACOM for any damages resulting from such improper use or sale.