







Customer Information Sheet

DRAWING No.: S1761-XXR SHEET 2 OF 2 IF IN DOUBT - ASK © NOT TO SCALE THIRD ANGLE PROJECTION ALL DIMENSIONS IN mm



COMPONENT SPECIFICATION:
MATERIAL = TITANIUM COPPER ALLOY.
FINISH:
42 = 0.76-1.27µ NICKEL ALL OVER,
0.05µ GOLD FLASH ON CONTACT AREA,
2.54µ MIN 100% TIN ON FOOT AREA
46 = 2.54µ MIN 100% TIN OVER 0.76-1.27µ NICKEL
RECOMMENDED WORKING HEIGHT = 2.50mm / MIN FORCE = 1.5N
MINIMUM WORKING HEIGHT = 1.75mm / MAX FORCE = 8.5N
ELECTRICAL:
CURRENT RATING = 4A
MECHANICAL:
DURABILITY = 1500 CYCLES
ENVIRONMENTAL:
OPERATING TEMPERATURE = -55°C TO +125°C



ORDER CODE:
S1761-XXR
FINISH:
42 = NICKEL ALL OVER,
GOLD FLASH ON CONTACT AREA
TIN ON FOOT AREA
46 = TIN OVER NICKEL ALL OVER

NOTES:
1. QUANTITY PER REEL = 2000.

MSP	9	23.21.16	20304
NAME	ISS.	DATE	C/NOTE
APPROVED:		M. PERREN	
CHECKED:		S. BENNETT	
DRAWN:		N. CODLING	
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN
www.harwin.com
technical@harwin.com

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL:
SEE ABOVE
FINISH: SEE ABOVE
S/AREA: mm²

TITLE:
S1761-XX EMI SHIELD FINGER
IN TAPE AND REEL
DRAWING NUMBER:
S1761-XXR
SHT
2 OF 2