



Material :
Insulator: PBT + G/F UL94V-0
Contact: Brass

RoHS COMPLIANT



K	ES101138			LEOCO CORPORATION GENERAL TOLERANCES: (UNLESS SPECIFIED) <table><tr><td></td><td>mm</td><td>inch</td></tr><tr><td>1 PLACE</td><td>± 0.30</td><td>± —</td></tr><tr><td>2 PLACES</td><td>± 0.20</td><td>± .012</td></tr><tr><td>3 PLACES</td><td>± 0.10</td><td>± .008</td></tr><tr><td>4 PLACES</td><td>± —</td><td>± .004</td></tr></table> ANGULAR ± (1°)		mm	inch	1 PLACE	± 0.30	± —	2 PLACES	± 0.20	± .012	3 PLACES	± 0.10	± .008	4 PLACES	± —	± .004	APPROVED:		PART NO.:			
	mm	inch																							
1 PLACE	± 0.30	± —																							
2 PLACES	± 0.20	± .012																							
3 PLACES	± 0.10	± .008																							
4 PLACES	± —	± .004																							
J	ES090318				DATE:		2540S****0*																		
I	ES070656				CHECKED:		TITLE: I.D.C. Socket																		
H	ES050752				DATE:		DRAWING NO.:																		
G	E010077				DRAWN:		254007S																		
REV.	ECO. NO.	CHG.	APP.		DATE:																				
							UNITS	SCALE	SIZE	SHEET	REV.														
							mm inch	2:1	A4	1/2	K														

A

B

C

D

E

A

B

C

D

E


Ordering Information :

2540S $\frac{**}{1} \frac{**}{2} \frac{**}{3} \frac{0*}{4}$

RoHS COMPLIANT

1. No. of circuits
2. Plating :
- T= Tin plated 120μ"min. over 30μ"min. nickel overall
- U= Gold flash over 30μ"min. nickel overall
- W= 15μ"min. gold flash over 30μ"min. nickel overall
- Z= 30μ"min. gold flash over 30μ"min. nickel overall
- F= Selective gold plated over 30μ"min. nickel overall
- J= 15μ"min. Selective gold plated over 30μ"min. nickel overall
- K= 30μ"min. Selective gold plated over 30μ"min. nickel overall
3. Options:
- 0= With Key
- N= Without Key
4. Color:
- 01= Black
- 09= Gray

Circuits	Dim.A	Dim.B	Dim.C	Dim.D
06	5.080(.200)	12.16(.479)	6.350(.250)	7.66(.302)
08	7.620(.300)	14.74(.580)	8.890(.350)	10.24(.403)
10	10.160(.400)	17.27(.680)	11.430(.450)	12.77(.503)
12	12.700(.500)	19.85(.781)	13.970(.550)	15.35(.604)
14	15.240(.600)	22.40(.882)	16.510(.650)	17.90(.705)
16	17.780(.700)	24.94(.982)	19.050(.750)	20.44(.805)
18	20.320(.800)	27.46(1.081)	21.590(.850)	22.95(.904)
20	22.860(.900)	30.00(1.181)	24.130(.950)	25.50(1.004)
24	27.940(1.100)	35.10(1.382)	29.210(1.150)	30.60(1.205)
26	30.480(1.200)	37.59(1.480)	31.750(1.250)	33.09(1.303)
30	35.560(1.400)	42.66(1.680)	36.830(1.450)	38.16(1.502)
34	40.640(1.600)	47.80(1.882)	41.910(1.650)	43.30(1.705)
36	43.180(1.700)	50.29(1.980)	44.450(1.750)	45.79(1.803)
40	48.260(1.900)	55.50(2.185)	49.530(1.950)	51.30(2.020)
44	53.340(2.100)	60.56(2.384)	54.610(2.150)	56.36(2.219)
50	60.960(2.400)	68.10(2.681)	62.230(2.450)	63.90(2.516)
56	68.580(2.700)	75.74(2.982)	69.850(2.750)	71.54(2.817)
60	73.660(2.900)	80.80(3.181)	74.930(2.950)	76.60(3.016)
62	76.200(3.000)	83.35(3.281)	77.470(3.050)	79.15(3.116)
64	78.740(3.100)	85.90(3.382)	80.010(3.150)	81.70(3.217)

K	ES101138			LEOCO CORPORATION GENERAL TOLERANCES: (UNLESS SPECIFIED) <table><tr><td></td><td>mm</td><td>inch</td></tr><tr><td>1 PLACE</td><td>± 0.30</td><td>± —</td></tr><tr><td>2 PLACES</td><td>± 0.20</td><td>± .012</td></tr><tr><td>3 PLACES</td><td>± 0.10</td><td>± .008</td></tr><tr><td>4 PLACES</td><td>± —</td><td>± .004</td></tr><tr><td colspan="3">ANGULAR ± (1°)</td></tr></table>		mm	inch	1 PLACE	± 0.30	± —	2 PLACES	± 0.20	± .012	3 PLACES	± 0.10	± .008	4 PLACES	± —	± .004	ANGULAR ± (1°)			APPROVED:		PART NO.:			
	mm	inch																										
1 PLACE	± 0.30	± —																										
2 PLACES	± 0.20	± .012																										
3 PLACES	± 0.10	± .008																										
4 PLACES	± —	± .004																										
ANGULAR ± (1°)																												
J	ES090318				DATE:		2540S****0*																					
I	ES070656				CHECKED:		TITLE:																					
				DATE:		I.D.C. Socket																						
H	ES050752			DRAWN:		DRAWING NO.:																						
G	E010077			DATE:		254007S																						
REV.	ECO. NO.	CHG.	APP.			UNITS mm inch	SCALE	SIZE	SHEET	REV.																		
							2:1	A4	2/2	K																		