

# MINIATURE TUBULAR TERMINALS

## PUSH-IN TERMINALS & PINS




.062 (1.57) – .067 (1.70)  
Mounting Holes

- Quick and Easy to Install
- Positive Locking In-Hole
- For Production or Prototype
- No Staking Required
- Holds .010 (.25) to .050 (1.27) Diameter Wire
- Terminals 1236 and 1237 have tapered socket spring forming that will hold multiple leads in place. Terminals are pre-tinned for easy soldering.

These terminals are often used for transistor and Bi-Pin lamp sockets. Terminals snap into place and are firmly held without the need of staking. Wire leads can be inserted from either end.



### INSERTION TOOL

For Arbor Press: **CAT. NO. TL-11**; For Hand Tool: **CAT. NO. 1214**




**MATERIAL:**  
.006 (.15) thick Brass.  
Pre-Tinned

**CAT. NO. 1236**



**MATERIAL:**  
.006 (.15) thick Brass.  
Pre-Tinned

**CAT. NO. 1237**




**MATERIAL:**  
.006 (.15) thick Brass.  
Pre-Tinned

**CAT. NO. 1238**

### “FLEA” CLIP



For subminiature applications where conventional terminals are too large or too costly. Ideal for quick repairs of printed circuitry. Simply insert wire through hole and it is held firmly by spring action assuring continued positive contact.



Mtg. Hole .062 (1.57)

Insertion Tool: **CAT. NO. 1322**


**MATERIAL:**  
.008 (.20) thick Beryllium Copper, Tin Plate

**CAT. NO. 1500**

### CLAMP TERMINAL



Terminal for production or prototype use. Holds as many as 7 leads without soldering, by spring action.



Mtg. Hole .093 (2.36)

Insertion Tool: **CAT. NO. 1323**


**MATERIAL:**  
.015 (.38) thick Spring Steel, Tin Plate

**CAT. NO. 1498CP**

### .025 SQUARE WIRE WRAP PINS

Completely burr free straight to within .003 (.08) per inch. Conical ends of square-wire with smooth blend-in radius on corners assures ease of insertion with minimum damage to pre-plated PCB holes.

CAT. NO.	L Length	CAT. NO.	L Length
5070	.400 (10.2)	5077	.642 (16.3)
5071	.440 (11.2)	5078	.675 (17.1)
5072	.515 (13.1)	5079	.720 (18.3)
5073	.535 (13.6)	5080	.850 (21.6)
5074	.600 (15.2)	5081	.916 (23.3)
5075	.618 (15.6)	5082	.995 (25.3)
5076	.625 (15.9)	5083	1.13 (28.7)




**MATERIAL:** Phosphor Bronze, Tin Plate

Tel (718) 956-8900 • Fax (718) 956-9040

(800) 221-5510 • [kec@keyelco.com](mailto:kec@keyelco.com)

**KEYSTONE®**

RoHS COMPLIANT — ISO 9001 CERTIFIED




**MATERIAL:** Brass, Nickel Plate

### “IMP” TERMINAL



Excellent for point to point or feed thru wiring. Slot is serrated to grip component leads. Multiple connections are made quick and easy.



Mtg. Hole .062 (1.57)

Insertion Tool: **CAT. NO. 1322**


**MATERIAL:**  
.008 (.20) thick Beryllium Copper, Tin Plate

**CAT. NO. 1499FT**

### “MICRO” TERMINAL



Easily press-fit into a .042 (1.07) diameter hole may be flared for permanent installation. Ideally designed for use in circuitry to support components when space is at a premium.



Insertion Tool: **CAT. NO. 1322**

**MATERIAL:**  
.008 (.20) thick Beryllium Copper, Tin Plate

**CAT. NO. 1495**

### CONTACT PINS (SEAMLESS)

Pins can be staked to .062 (1.57) and .093 (2.36) thick boards.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Keystone Electronics:](#)

[1214](#) [1323](#) [1322](#)