






PRODUCT NUMBER
SEE TABLE



RECOMMENDED PCB LAYOUT
(ALL HOLES LOCATED ON .100 [2.54] GRID
UNLESS OTHERWISE SPECIFIED)

NOTES:

1. PRODUCT NUMBERING CODE:
50001 - X YYY Z LF
LEAD FREE (OPTIONAL)
TAIL LENGTH SEE TABLE
NO. OF POSITIONS SEE NOTE 2
PLATING SEE TABLE
BASE NUMBER

PRODUCT NUMBERING CODE FOR
SELECT LOAD PART NUMBERS:

- 50001 - XXYYY LF
LEAD FREE (OPTIONAL)
SEQUENCE NUMBER
ALWAYS 'XX'
BASE NUMBER

- ② THIS PRODUCT IS CONFIGURED IN SIZES OF
20 THRU 122 COLUMNS IN INCREMENTS OF TWO.
i.e.: 20,22,24,26.....118,120,122.
- ③ HOUSING MATERIAL: GLASS AND MINERAL FILLED THERMOPLASTIC.
CONTACT MATERIAL: BeCu
- ④ COMPANY NAME, PART NUMBER AND LOT CODE TO APPEAR
ON THIS SURFACE PER BUS-12-108.
- ⑤ LENGTH FORMUALS:
DIM A= .100/2.54 X NO. OF COLUMNS + 1.05/26.7
DIM B= .100/2.54 X NO. OF COLUMNS + .750/19.05
DIM C= .100/2.54 X NO. OF COLUMNS DIVIDED BY 2 - .100/2.54
6. PRODUCT WITH "LF" SUFFIX MEETS EUROPEAN UNION
DIRECTIVES AND OTHER COUNTRY REGULATIONS AS
DESCRIBED IN GS-22-008.
7. THIS HOUSING (WITH "LF" SUFFIX) WILL WITHSTAND
EXPOSURE TO 260°C PEAK TEMPERATURES FOR
10-30 SECONDS IN A CONVECTION, INFRA-RED
OR VAPOR PHASE REFLOW OVEN.
- ⑧ PLATING OPTION:
MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.

mat'l. code SEE NOTE 3				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HPC			
ltr	ecn no	dr	date	tolerances unless otherwise specified		scale 1:1	title 3 ROW R/A RECEPTACLE SOLDER TAIL, 1 GUIDE PIN			
P				angles	linear					
				dr	D. HORCHLER	10/18/05	Amphenol FCi	dwg no		sheet 2 of 3
				enr	T. BREWBAKER	10/18/05		50001		size A3
				chr	M JACOB	08/12/17				
				appd	BIJU K PAUL	08/12/17		type Product Customer Drawing		
sheet index	revision sheet									

