





DS2107A
SCSI Terminator


FEATURES

- Fully compliant with SCSI and SCSI-2 standards
- Backward compatible to the DS2107S
- Provides active termination for 9 signal lines
- Laser-trimmed 110 ohm termination resistors have 1% tolerance
- Low dropout voltage
- Power-down mode isolates termination resistors from the bus
- Handles actively negated SCSI signals
- Onboard thermal shutdown circuitry
- 16-pin plastic SOIC (DS2107AS) and 20-pin plastic thin SSOP (DS2107AE)

PIN ASSIGNMENT



ACTUAL FOOTPRINT SIZE



DESCRIPTION

The SCSI-2 standard recommends the use of active terminations at both ends of every cable segment in a SCSI system with single-ended drivers and receivers. The DS2107A SCSI Terminator, which is fully compliant with the standard, enables the designer to gain the benefits of active termination: greater immunity to voltage drops on the TERNPWR (TERMination PoWeR)

line, enhanced high-level noise immunity, intrinsic TERNPWR decoupling, and very low quiescent current consumption. The DS2107A integrates a regulator and nine precise switched 110 ohm termination resistors into a monolithic IC.


FUNCTIONAL DESCRIPTION


The DS2107A consists of a bandgap reference, buffer amplifier, and nine termination resistors (Figure 1). The bandgap reference circuit produces a precise 2.55V level which is fed to a buffer amplifier. The buffer produces a 2.85V level and is capable of sourcing at least 24 mA into each of the termination resistors when the signal line is low (active). When the driver for a given signal line turns off, the terminator will pull the signal line to 2.85V (quiescent state). To handle actively negated SCSI signals, the buffer can sink 200 mA. When all lines settle in the quiescent state, the regulator will consume about 5 mA. When the DS2107A is put into power-down mode by bringing $\overline{\text{PD}}$ low, the power-down circuitry will turn off the transistors on each signal line. This will isolate the DS2107A from the signal lines and effectively remove it from the circuit. The power-down pin ($\overline{\text{PD}}$)

has an internal 50K ohm pull-up resistor. To place the DS2107A into an active state, the $\overline{\text{PD}}$ pin should be left open circuited.

To ensure proper operation, both the TERMPWR1 and TERMPWR2 pins must be connected to the SCSI bus TERMPWR line and both the VREF1 and VREF2 pins must be tied together externally. Each DS2107A requires parallel 0.1 μF and 4.7 μF capacitors connected between the VREF pins and ground. Figure 2 details a typical SCSI bus configuration. In an 8-bit wide SCSI bus arrangement ("A" Cable), two DS2107A's would be needed at each end of the SCSI cable in order to terminate the 18 active signal lines. In a 16-bit wide SCSI bus arrangement ("P" Cable), three DS2107A's would be needed at each end of the SCSI cable in order to terminate the 27 active signal lines.

DS2107A BLOCK DIAGRAM Figure 1



TYPICAL SCSI BUS CONFIGURATION Figure 2**NOTES:**

1. C1 = 0.1 μ F ceramic
C2 = 4.7 μ F tantalum
C3 = 2.2 μ F tantalum or 4.7 μ F aluminum
2. If the DS2107A is to be embedded into a peripheral that will act as a target on a SCSI bus, it is recommended that TERMPWR be derived from the SCSI cable, not generated locally. In this configuration, if a power failure occurs in the peripheral, it will not affect the bus.

PIN DESCRIPTION Table 1

| DS2107AE PIN | DS2107AS PIN | SYMBOL | DESCRIPTION |
|-----------------|-----------------|----------|--|
| 1 | 1 | TERMPWR1 | Termination Power 1. Should be connected to the SCSI TERMPWR line. Must be decoupled with either a 2.2 μ F or 4.7 μ F. See Figure 2. |
| 3 | 2 | R1 | Signal Termination 1. 110 ohm termination. |
| 4 | 3 | R2 | Signal Termination 2. 110 ohm termination. |
| 5 | 4 | R3 | Signal Termination 3. 110 ohm termination. |
| 6 | 5 | R4 | Signal Termination 4. 110 ohm termination. |
| 7 | 6 | R5 | Signal Termination 5. 110 ohm termination. |
| 9 | 7 | VREF1 | Reference Voltage 1. Must be externally connected directly to the VREF2 pin. Must be decoupled with a 4.7 μ F and a 0.1 μ F as shown in Figure 2. |
| 10 | 8 | GND | Ground. Signal ground; 0.0V. |
| 11 | 9 | TERMPWR2 | Termination Power 2. Should be connected to the SCSI TERMPWR line. Must be decoupled with either a 2.2 μ F or 4.7 μ F. See Figure 2. |
| 13 | 10 | R6 | Signal Termination 6. 110 ohm termination. |
| 14 | 11 | R7 | Signal Termination 7. 110 ohm termination. |
| 15 | 12 | R8 | Signal Termination 8. 110 ohm termination. |
| 16 | 13 | R9 | Signal Termination 9. 110 ohm termination. |
| 17 | 14 | NC | No Connect. Do not connect any signal to this pin. |
| 19 | 15 | VREF2 | Reference Voltage 2. Must be externally connected directly to the VREF1 pin. Must be decoupled with a 4.7 μ F and a 0.1 μ F as shown in Figure 2. |
| 20 | 16 | PD | Power Down. When tied low, the DS2107A enters a power-down mode. Contains an internal 50K pull-up. Strap low to deactivate the DS2107A, leave open circuited to activate the DS2107A. |
| 2,8,12,18 | N/A | HS-GND | Heat Sink Ground. Internally connected to the mounting pad. Should be either grounded or electrically isolated from other circuitry. |

ABSOLUTE MAXIMUM RATINGS*

| | |
|---------------------------------------|----------------------|
| Voltage on Any Pin Relative to Ground | -1.0V to +7.0V |
| Operating Temperature | 0°C to +70°C |
| Storage Temperature | -55°C to 125°C |
| Soldering Temperature | 260°C for 10 seconds |

* This is a stress rating only and functional operation of the device at these or any other conditions above those indicated in the operation sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods of time may affect reliability.

RECOMMENDED OPERATING CONDITIONS

(0°C to 70°C)

| PARAMETER | SYMBOL | MIN | TYP | MAX | UNITS | NOTES |
|--------------------------|-----------|------|-----|----------------|-------|-------|
| TERMPWR Voltage | V_{TP} | 4.00 | | 5.25 | V | |
| \overline{PD} Active | V_{PDA} | -0.3 | | 0.8 | V | |
| \overline{PD} Inactive | V_{PDI} | 2.0 | | $V_{TP} + 0.3$ | V | |

DC CHARACTERISTICS

(0°C to 70°C)

| PARAMETER | SYMBOL | MIN | TYP | MAX | UNITS | NOTES |
|------------------------------------|------------|-----|-----|-----|---------|---------|
| TERMPWR Current | I_{TP} | | 5 | 250 | mA | 1,3 |
| | I_{TP} | | | 8 | mA | 1,4 |
| Power Down Current | I_{PD} | | 100 | | μ A | 1,2,5 |
| Termination Resistance | R_{TERM} | 108 | 110 | 112 | ohms | 1,2 |
| Die Thermal Shutdown | T_{SD} | | 150 | | °C | 1 |
| Power Down Termination Capacitance | C_{PD} | | 8.5 | 10 | pF | 1,2,5,6 |
| \overline{PD} Hysteresis | H_{PD} | | 280 | | mV | 1 |

REGULATOR CHARACTERISTICS


(0°C to 70°C)

| PARAMETER | SYMBOL | MIN | TYP | MAX | UNITS | NOTES |
|------------------|------------|------|------|------|-------|-------|
| Output Voltage | V_{REF} | 2.79 | 2.85 | 2.91 | V | 1,2 |
| Drop Out Voltage | V_{DROP} | | 0.75 | 1.0 | V | 3,6 |
| Line Regulation | L_{REG} | | 1.0 | 2.0 | % | 1,4,6 |
| Load Regulation | L_{OREG} | | 1.3 | 3.0 | % | 1,2,6 |
| Current Limit | I_{LIM} | 300 | 350 | 400 | mA | 1 |
| Sink Current | I_{SINK} | | 200 | | mA | 1 |

NOTES:


1. 4.00V < TERMPWR < 5.25V.
2. 0.0V < signal lines < 3.0V.
3. All signal lines = 0.0V.
4. All signal lines open.
5. \overline{PD} = 0.0V.
6. Guaranteed by design; not production tested.

DS2107AS SCSI TERMINATOR 16-PIN SOIC (300 MIL)



| PKG | 16-PIN | |
|-------|-----------|-------|
| | DIM | |
| | MIN | MAX |
| A IN. | 0.402 | 0.412 |
| MM | 10.21 | 10.46 |
| B IN. | 0.290 | 0.300 |
| MM | 7.37 | 7.65 |
| C IN. | 0.089 | 0.095 |
| MM | 2.26 | 2.41 |
| E IN. | 0.004 | 0.012 |
| MM | 0.102 | 0.30 |
| F IN. | 0.094 | 0.105 |
| MM | 2.38 | 2.68 |
| G IN. | 0.050 BSC | |
| MM | 1.27 BSC | |
| H IN. | 0.398 | 0.416 |
| MM | 10.11 | 10.57 |
| J IN. | 0.009 | 0.013 |
| MM | 0.229 | 0.33 |
| K IN. | 0.013 | 0.019 |
| MM | 0.33 | 0.48 |
| L IN. | 0.016 | 0.040 |
| MM | 0.40 | 1.02 |
| phi | 0° | 8° |

DS2107AE SCSI TERMINATOR 20-PIN TSSOP (PRELIMINARY)



| DIM | MIN | MAX |
|-------|----------|------|
| A MM | — | 1.10 |
| A1 MM | 0.05 | — |
| A2 MM | 0.75 | 1.05 |
| C MM | 0.09 | 0.18 |
| L MM | 0.50 | 0.70 |
| e1 MM | 0.65 BSC | |
| B MM | 0.18 | 0.30 |
| D MM | 6.40 | 6.90 |
| E MM | 4.40 NOM | |
| G MM | 0.25 REF | |
| H MM | 6.25 | 6.55 |
| phi | 0° | 8° |