

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-.-

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC

HB


DIST

-

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
C		OBSOLETE P/N ECO-09-014329	28Jul2009	YS.H	BH.Y
D		CHANGE LOGO&ADD LINE IDENTIFICATION ECO-12-003498 & ADD CQC SYMBOL P-11-003756	08Nov2012	YS.H	BH.Y

CONNECTION DIAGRAM (BOTTOM VIEW)



DRILLING DIAGRAM (BOTTOM VIEW)






Diagram dimension	Tolerance
0.99mm max.	±0.1mm
1 - 2.99mm	±0.2mm
3mm min.	±0.3mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
	ANGLES ± -
MATERIAL	FINISH
-	-

DWN	KY.DU	TE Connectivity			
CHK	N.Funayama				
APVD	C.H.Hsu	NAME			
PRODUCT SPEC	-				
APPLICATION SPEC	-	PCH-L2M(H)-WG CUSTOMER DRAWING			
WEIGHT	-				
CUSTOMER DRAWING	SCALE	5:1	SHEET	1 of 2	REV D

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-.-

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

HB

-

P

LTR

DESCRIPTION

DATE

DWN

APVD

- SEE SHEET 1

-

-

-

1-1721768-5	PCH-124L2M-WG	24V	PCH-124L2M-WG	107-79046(TUBE)	o	ACTIVE
1-1721768-4	PCH-148L2MH-WG	48V	PCH-148L2MH-WG	107-79019(TRAY)	n	OBSOLETE
1-1721768-3	PCH-124L2MH-WG	24V	PCH-124L2MH-WG	107-79019(TRAY)	m	OBSOLETE
1-1721768-2	PCH-112L2MH-WG	12V	PCH-112L2MH-WG	107-79019(TRAY)	l	OBSOLETE
1-1721768-1	PCH-109L2MH-WG	9V	PCH-109L2MH-WG	107-79019(TRAY)	k	OBSOLETE
1-1721768-0	PCH-106L2MH-WG	6V	PCH-106L2MH-WG	107-79019(TRAY)	j	OBSOLETE
1721768-9	PCH-105L2MH-WG	5V	PCH-105L2MH-WG	107-79019(TRAY)	i	OBSOLETE
1721768-8	PCH-103L2MH-WG	3V	PCH-103L2MH-WG	107-79019(TRAY)	h	OBSOLETE
1721768-7	PCH-148L2M-WG	48V	PCH-148L2M-WG	107-79019(TRAY)	g	ACTIVE
1721768-6	PCH-124L2M-WG	24V	PCH-124L2M-WG	107-79019(TRAY)	f	ACTIVE
1721768-5	PCH-112L2M-WG	12V	PCH-112L2M-WG	107-79019(TRAY)	e	ACTIVE
1721768-4	PCH-109L2M-WG	9V	PCH-109L2M-WG	107-79019(TRAY)	d	ACTIVE
1721768-3	PCH-106L2M-WG	6V	PCH-106L2M-WG	107-79019(TRAY)	c	ACTIVE
1721768-2	PCH-105L2M-WG	5V	PCH-105L2M-WG	107-79019(TRAY)	b	ACTIVE
1721768-1	PCH-103L2M-WG	3V	PCH-103L2M-WG	107-79019(TRAY)	a	ABSOLUTE
TE PART NO	TE TYPE NAME	PART B	PART A	PACKAGE SPEC	TYPE	P/N STATUS

RELAY TYPE

©

NOTES:

1.LAST SUFFIX
NON : WASHABLE TYPE

② 2.LOT NO SYSTEM AS FOLLOWING:



WEEK

YEAR

© 3.TERMINAL DIMENSION IS BEFORE SOLDER DIP;

© 4.FOR THE TIN-PLATING OF THE PINS:

+0.1mm FOR WIDTH,THICKENSS AND DIAMETER.

+0.5mm FOR LENGTH.

© 5.MARKING FROM INK TO LASER.

© 6.ADD LOT NO. SYSTEM AS FOLLOWING;



I, DIGITS FOR DAY OF THE WEEK

1...MONDAY IN THIS WEEK;

2...TUESDAY IN THIS WEEK;

7...SUNDAY IN THIS WEEK

II, DIGITS FOR SHIFT OF THE DAY

1...DAY SHIFT IN THIS DAY;

2...NIGHT SHIFT IN THIS DAY;

III, ONE CHARACTER DISTINGUISH THE LINE IDENTITY, SUCH AS: A,B,...Z

		UV RESIN	UV SEAL	16
		EPOXY RESIN	SEAL	15
CLASS F ④		MW79 ④	MAGNETIC WIRE	14
	SOLDER DIP	CP WIRE	COIL TERMINAL	13
		Ag ALLOY	STATONARY CONTACT	12
		Ag ALLOY	MOVABLE CONTACT	11
		Cu ALLOY	HINGE SPRING	10
	SOLDER DIP	Cu ALLOY	NO TERMINAL	9
	SOLDER DIP	Cu ALLOY	MOVABLE SPRING	8
UL 94V-0		LCP	CARD	7
UL 94V-0		PET	CASE	6
UL 94HB		PA NYLON	BOBBIN	5
UL 94V-0		PET	BASE	4
	Ni PLATED	STEEL	CORE	3
	CuNi PLATED	STEEL	ARMATURE	2
	CuNi PLATED	STEEL	YOKE	1
INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	KY.DU	
		CHK	-	
		N.Funayama		
DIMENSIONS: mm		APVD	C.H.Hsu	
		PRODUCT SPEC	-	
		APPLICATION SPEC	-	
		WEIGHT	-	
MATERIAL	FINISH	-		
CUSTOMER DRAWING		SCALE 5:1		SHEET 2 OF 2

TE Connectivity	
NAME	
PCH-L2M(H)-WG CUSTOMER DRAWING	
SIZE	CAGE CODE
A3	00779
DRAWING NO	RESTRICTED TO
C=1721768	-
REV D	