


SF1108 120 MHz SAW Filter



PRELIMINARY

- Designed for CDMA IS-95 Receiver IF Applications
- Simple External Impedance Matching
- Hermetic Metal DIP
- Unbalanced Input and Output



Characteristic	Sym	Min	Typ	Max	Units	Notes
Nominal Center Frequency	fc		120.000		MHz	1
Passband	Insertion Loss at fc		15	20.0	dB	1, 2
	1.5 dB Passband					
	BW _{1.5}	±450	±480		kHz	
	Phase Linearity over fc ±450 kHz		8	20	°P-P	
Rejection	Triple Transit Rejection		42		dB	1, 2, 3
	fc-900 to fc-875 and fc+875 to fc+900 kHz	35	45			
	At fc ±900 kHz	50	54			
	10 MHz to fc-900 kHz and fc+900 kHz to 500 MHz	50	51			
Operating Temperature Range	T _A	-20		+70	°C	1

Impedance Matching to 50 Ω unbalanced	External L-C
Case Style	DIP18-8 27.2 x 12.6 mm Nominal Footprint
Lid Symbolization (YY = year, WW = week)	RFM SF1108 YYWW

Absolute Maximum Ratings

Rating	Value	Units
Maximum Incident Power in Passband	+10	dBm
Max. DC voltage between any 2 terminals	30	VDC
Storage Temperature Range	-40 to +85	°C
Max Soldering Profile	265°C for 10 s	

Electrical Connections (See note 3)

Connection	Terminals
Port 1 Hot	18
Port 1 Gnd Return	1
Port 2 Hot	9
Port 2 Gnd Return	10
Case Ground	All others

Notes:

1. Unless noted otherwise, all specifications apply over the operating temperature range with filter soldered to the specified demonstration board with appropriate external impedance matching to 50 Ω and measured with 50 Ω network analyzer.
2. Unless noted otherwise, all frequency specifications are referenced to the nominal center frequency, fc.
3. Rejection is measured as attenuation below the minimum IL point in the passband. Rejection in final user application is dependent on PCB layout and external impedance matching design. See Application Note No. 42 for details. All "NC" or "no connection pins" should be grounded.
4. "LRIP" or "L" after the part number indicates "low rate initial production" and "ENG" or "E" indicates "engineering prototypes."
5. The design, manufacturing process, and specifications of this filter are subject to change.
6. Either Port 1 or Port 2 may be used for either input or output in the design. However, impedances and impedance matching may vary between Port 1 and Port 2, so that the filter must always be installed in one direction per the circuit design.
7. US and international patents may apply.
8. RFM, stylized RFM logo, and RF Monolithics, Inc. are registered trademarks of RF Monolithics, Inc.
9. ©Copyright 1999, RF Monolithics Inc.
10. Electrostatic Sensitive Device. Observe precautions for handling.





RF Monolithics, Inc.
4347 Sigma Road
Dallas, Texas 75244
USA

Phone: +1(972)233-2903
Fax: +1(972)387-8148
e-mail: info@rfm.com
Home page: www.rfm.com

European Sales Office
44 1963 251383
44 1963 251510

SF1108 120 MHz SAW Filter




RF Monolithics, Inc.
4347 Sigma Road
Dallas, Texas 75244
USA

Phone: +1(972)233-2903
Fax: +1(972)387-8148
e-mail: info@rfm.com
Home page: www.rfm.com

European Sales Office
44 1963 251383
44 1963 251510

Metal 8-Pin DIP in 18-Pin Configuration 27.2 x 12.6 mm Nominal Footprint



Dimension	mm			Inches		
	Min	Nom	Max	Min	Nom	Max
A		27.18	27.56		1.070	1.085
B		12.55	12.95		0.494	0.510
C		3.56	5.08		0.140	0.200
D	0.41	0.48	0.51	0.016	0.019	0.020
E		20.32			0.800	
F		7.62			0.300	
K	3.30	3.81	6.73	0.130	0.150	0.265
L	1.37	1.45	1.52	0.054	0.057	0.060
P		2.54			0.100	
R		2.03			0.080	

