



Features

- Through-hole and SMD styles available
- Available sharp click feel with a positive tactile feedback
- Ultra-miniature and lightweight structure suitable for high density mounting
- Designed for washing after soldering
- RoHS compliant*



- Insert molding in the contact with special treatment prevents flux buildup during soldering and permits autodipping

ST(H,M,J,R)W Series Sealed Tact Switch

Electrical Characteristics

Electrical Life100,000 cycles min.
 RatingDC 12 V, 50 mA
 Contact Resistance100 mohms max.
 Insulation Resistance ..100 Mohms min.
 DC 500 V min.

Dielectric Strength

.....AC 250 V for 1 minute
 Contact Arrangement...1 pole 1 position


Environmental Characteristics

Mechanical Life100,000 cycles min.
 Operation Force160 g, 260 g
 Tolerance±50 g
 Stop Strength ..Place the switch vertical, a static load of 3 kg shall be applied in the direction of actuator operation for a period of 15 seconds
 Stroke0.25 mm (+0.2 mm, -0.1 mm)
 Operating Temperature Range-25 °C to +70 °C
 Storage Temperature Range-30 °C to +80 °C
 Vibration TestMIL-STD-202F, Method 201A
 Frequency10-55-10 Hz/1 minute
 DirectionsX,Y,Z 3 mutually perpendicular directions
 Time.....2 hours each direction, high reliability
 Shock TestMIL-STD-202F, Method 213B, Condition A
 Gravity50 g (peak value), 11 msec.
 Directions/Time6 sides and 3 times in each direction

Physical Characteristics


Cover MaterialsStainless steel
 Base Materials.....Thermoplastic LCP
 UL94V-0 black
 Actuator MaterialsThermoplastic
 Nylon UL94V-0 (680, 690)
 Color.....Brown (Silver 680 type)
 Contact Disc. MaterialsPhosphor bronze with gold cladding
 Terminal MaterialsBrass with silver cladding

CIRCUIT DIAGRAM




Product Dimensions


STHW




STJW



STMW



STRW



DIMENSIONS: $\frac{\text{MM}}{(\text{IN})}$


*RoHS Directive 2002/95/EC Jan 27 2003 including Annex.
 Specifications are subject to change without notice.
 Customers should verify actual device performance in their specific applications.

ST(H,M,J,R)W Series Sealed Tact Switch


BOURNS®

Packaging Specifications


STJW
STMW



STMW
STJW
STHW



STRW



DIMENSIONS: $\frac{\text{MM}}{(\text{INCHES})}$

How to Order

STM W - 6 60 - N TR

Model
STM = SMD "G" style
STH = Through-hole
STJ = SMD "J" style
STR = SMD right angle

Product Type
W = Washable

Size
6 = 6 mm

Height (STM, STH, STJ)

50 = $\frac{3.5}{(0.14)}$ (N, R, V)

60 = $\frac{3.1}{(0.12)}$ (N)

67 = $\frac{5.2}{(0.20)}$ (N, R, V)

80 = $\frac{2.3}{(0.09)}$ (S)

90 = $\frac{3.8}{(0.15)}$ (N, R, V)

Height (STR)

10 = 0 (N, R)

20 = 0.8 (N, R)

30 = 1.0 (N, R)

40 = 2.3 (N, R)

Actuating Force

S = 160 g (Silver head)

N = 160 g (Brown head)

R = 260 g (Red head)

V = 360 g (Clear head)

Packaging Option

TR = Embossed tape (STM, STJ, STR only)

610/620/630/640 = 700 pcs.

650 = 1900 pcs.

660 = 2000 pcs.


667 = 900 pcs.

680 = 2000 pcs.

690 = 1900 pcs.

___ = 75 pcs./tube (STM, STJ, STH only)

Reflow Soldering Profile



REV. 02/06

Specifications are subject to change without notice.
Customers should verify actual device performance in their specific applications.

OBSOLETE