








LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	RELEASED PER RTS 359806.1	04AUG2010	WS	RP

PART NO. 	"A°"	HOUSING	CONTACT
1410338-1	0°		
1410338-2	45°		
1410338-3	90°		
1410338-4	270°		
1410338-5	315°		
1410338-6			



- 1 MATERIAL: HOUSING: ZINC ALLOY DIE CASTING,
ZAMAK 3.
CONTACT: PHOSPHOR BRONZE
- 2 HOLE FOR POSITIVE RETENTION SCREW.
- 3 DASH NUMBERS INDICATE KEY ORIENTATION
(P/N 1410338-2 SHOWN ON DRAWING)
- 4 GROUND PAD $\varnothing 5\text{mm}$ ON BOTH SIDE OF PCB.
- 5 FINISH: $3.0\mu\text{m}$ MIN NICKEL OVER COPPER
- 6 CONTACT FINISH: $1.27\mu\text{m}$ MINIMUM NICKEL ALL OVER
- 7 GUIDE MODULE W/O KEYING
GUIDE PIN 1410337 SERIES MUST BE ORIENTED
TO PROVIDE PROPER ESD PERFORMANCE



7.25	1410338
DIM X ADJACENT TO TIER 1 OR TIER 2 ASSEMBLY	PART NO

PRIMARY PCB LAYOUT
CONNECTOR SIDE
SCALE 3: 1

'Y'	PRODUCT
2.5	TIER 1
2.25	TIER 2
1.50	TIER 2 (7-ROW)

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN 04AUG2010 W. SOURBEER		Tyco Electronics		Tyco Electronics Harrisburg, PA 17105-3608	
CHK 04AUG2010 B. PATTERSON		APVD		NAME MULTIGIG GUIDE MODULE/STANDOFF, RIGHT ANGLE, 20.3mm, DAUGHTERCARD			
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.01 1 PLC ±.05 2 PLC ±.13 3 PLC ±.01 4 PLC ±.0001 ANGLES ±.001		PRODUCT SPEC 108-2072		APPLICATION SPEC 114-13056	
MATERIAL 		FINISH  		WEIGHT -		RESTRICTED TO -	
SIZE A2		CAGE CODE 00779		DRAWING NO C-1410338		CUSTOMER DRAWING	
SCALE 4		SHEET 1		OF 1		REV A	