



ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART, CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG


REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398


DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1891	A	RELEASED	EO	06/27/06	SA	7/25/06	HO	7/25/06
2020	B	Jacket material corrected	jwm	2/5/10	jwm	2/5/10	jwm	2/5/10



RoHS
Compliant



Telephone Flat Cable
Bare Copper Stranded
Polypropylene Insulated
PVC Jacket



SPECIFICATIONS:

1. Insulation:

Conductor	Insulation		Color Code		
AWG	Material	O.D.	1. WHITE	2. BLACK	3. RED
24(11/0.16)	PP	0.95±0.05mm	4. GREEN	5. YELLOW	6. BLUE

2. Jacket:

Material	O.D.	Color
PVC	2.4X7.0±0.1mm	SILVER SATIN

3. Electrical & Physical Properties

- Temperature & Voltage Rating: 60°C – 150V
- Conductor Resistance: 93 Ohm/1000 Meters Max. at 20°C
- Insulation Resistance: 100 Megohm/1000 Meters Min. at 20°C
- Dielectric Strength: 500 VAC for One Minute

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED
HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE
BELIEVE TO BE ACCURATE AND RELIABLE. SINCE
CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE
USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT
FOR THE INTENDED USE AND ASSUME ALL RISK AND
LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
Unless Otherwise
Specified
.X ±0.2 [0.008]
.XX ±0.12 [0.005]

DRAWN BY:
EKLAS ODISH
DATE:
06/27/06
CHECKED BY:
DATE:
7/25/06
APPROVED BY:
DATE:
7/25/06
HISHAM ODISH

DRAWING TITLE:
Flat Telephone Cable, 24 AWG, 6 Stranded Conductors, 100FT, RoHS
SIZE DWG. NO. ELECTRONIC FILE REV
A SPC19813 84K8575.DWG B
SCALE: NTS U.O.M.: mm [INCHES] SHEET: 1 OF 1