




Features:

Designed for general-purpose amplifier and low speed switching applications

- Collector-Emitter sustaining voltage
 - $V_{CEO(sus)}$ = 60 V (Minimum) - TIP145
 - = 80 V (Minimum) - TIP141, TIP146
 - = 100 V (Minimum) - TIP142, TIP147
- Collector-Emitter saturation voltage
 - $V_{CE(sat)}$ = 2 V (Maximum) at $I_C = 5 A$
- Monolithic construction with Built-in Base-Emitter shunt resistor



Pin 1. Base
2. Collector
3. Emitter

Dimensions	Minimum	Maximum
A	20.63	22.38
B	15.38	16.2
C	1.9	2.7
D	5.1	6.1
E	14.81	15.22
F	11.72	12.84
G	4.2	4.5
H	1.82	2.46
I	2.92	3.23
J	0.89	1.53
K	5.26	5.66
L	18.5	21.5
M	4.68	5.36
N	2.4	2.8
O	3.25	3.65
P	0.55	0.7

Dimensions : Millimetres

NPN **PNP**
TIP141 **TIP145**
TIP142 **TIP146**
 TIP147

10 Amperes
Darlington
Complementary
Silicon
Power Transistors
60 - 100 V
125 W




TO-247 (3P)

Maximum Ratings

Characteristic	Symbol	TIP145	TIP141 TIP146	TIP142 TIP147	Unit
Collector - Emitter Voltage	V _{CEO}	60	80	100	V
Collector - Base Voltage	V _{CBO}				
Emitter - Base Voltage	V _{EBO}	5			
Collector Current - Continuous - Peak	I _C I _{CM}	10 15			A
Base Current	I _B	0.5			
Total Power Dissipation at T _C = 25°C Derate above 25°C	P _D	125 1			W W / °C
Operating and Storage Junction Temperature Range	T _J , T _{STG}	-65 to +150			°C

Thermal Characteristics

Characteristic	Symbol	Maximum	Unit
Thermal Resistance Junction to case	$R_{\theta jc}$	1	$^\circ\text{C} / \text{W}$



Electrical Characteristics ($T_C = 25^\circ\text{C}$ unless otherwise specified)

Characteristic	Symbol	Minimum	Maximum	Unit
OFF Characteristics				
Collector - Emitter Sustaining Voltage (1) ($I_C = 30 \text{ mA}$, $I_B = 0$) TIP145 TIP141, TIP146 TIP142, TIP147	$V_{CEO(sus)}$	60 80 100	-	V
Collector Cut off Current ($V_{CE} = 30 \text{ V}$, $I_B = 0$) TIP145 ($V_{CE} = 40 \text{ V}$, $I_B = 0$) TIP141, TIP146 ($V_{CE} = 50 \text{ V}$, $I_B = 0$) TIP142, TIP147	I_{CEO}	-	2 2 2	mA
Collector Cut off Current ($V_{CB} = 60 \text{ V}$, $I_E = 0$) TIP145 ($V_{CB} = 80 \text{ V}$, $I_E = 0$) TIP141, TIP146 ($V_{CB} = 100 \text{ V}$, $I_E = 0$) TIP142, TIP147	I_{CBO}	-	1 1 1	
Emitter Cut off Current ($V_{EB} = 5 \text{ V}$, $I_C = 0$)	I_{EBO}	-	2	

Darlington Transistors

Electrical Characteristics ($T_C = 25^\circ\text{C}$ unless otherwise specified)


ON Characteristics (1)				
DC Current Gain ($I_C = 5\text{ A}$, $V_{CE} = 4\text{ V}$) ($I_C = 10\text{ A}$, $V_{CE} = 4\text{ V}$)	h_{FE}	1,000 500	-	-
Collector - Emitter Saturation Voltage ($I_C = 5\text{ A}$, $I_B = 10\text{ mA}$) ($I_C = 10\text{ A}$, $I_B = 40\text{ mA}$)	$V_{CE(\text{sat})}$	-	2 3	V
Base - Emitter Saturation Voltage ($I_C = 10\text{ A}$, $I_B = 40\text{ mA}$)	$V_{BE(\text{sat})}$	-	3.5	
Base - Emitter On Voltage ($I_C = 10\text{ A}$, $V_{CE} = 4\text{ V}$)	$V_{BE(\text{on})}$	-	3	

Switching Characteristics					
Delay Time	$V_{CC} = 30\text{ V}$, $I_C = 5\text{ A}$ $I_{B1} = -I_{B2} = 20\text{ mA}$ $t_p = 20\text{ }\mu\text{s}$, Duty cycle $\leq 2\%$	t_d	0.15 (Typical)	-	μs
Rise Time		t_r	0.55 (Typical)	-	
Storage Time		t_s	2.5 (Typical)	-	
Fall Time		t_f		-	


1. Pulse Test : Pulse width = 30 μs , Duty cycle = 2%

Internal Schematic Diagram


NPN : TIP141, TIP142



PNP : TIP145, TIP146, TIP147




Active Region Safe Operating Area (SOA)



There are two limitations on the power handling ability of a transistor: average junction temperature and second breakdown. Safe operating area curves indicate $I_C - V_{CE}$ limits of the transistor that must be observed for reliable operation i.e., the transistor must not be subjected to greater dissipation than curves indicate. The data of SOA curve is based on $T_{J(PK)} = 150^\circ\text{C}$; T_C is variable depending on conditions. At high case temperatures, thermal limitation will reduce the power that can be handled to values less than the limitations imposed by second breakdown.


Darlington Transistors

Small-Signal Common-Emitter Forward Current Transfer Ratio




NPN : TIP141, TIP142

Switching Time




Unclamped Inductive Load




PNP : TIP145, TIP146, TIP147


Switching Time



DC Current Gain



DC Current Gain




Darlington Transistors




NPN : TIP141, TIP142

Collector - Emitter Saturation Voltage




PNP : TIP145, TIP146, TIP147


Collector - Emitter Saturation Voltage



Base - Emitter Voltage



Base - Emitter Voltage



Specification Table

I_C (A)	V_{CEO} Maximum (V)	h_{FE} Minimum at $I_C = 5 A$	P_{tot} at 25°C (W)	Package	Type	Part Number
10	80	1,000	125	TO-247 (3P)	NPN	TIP141
	100					TIP142
	60				PNP	TIP145
	80					TIP146
	100					TIP147

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.