

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT -- By -- ALL RIGHTS RESERVED.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G3	REVISED PER ECO-12-003796	28FEB12	KH	DR
	G4	REVISED PER ECO-17-008806	20FEB2018	RS	DR

D

C

B

A



AMP
WIRE RANGE

22-16 AWG
SOLID OR STRANDED

- 1
- STAMP AMP 22-18 APPROX AS SHOWN 22-16 TERMINALS ARE STAMPED 22-18 IN ACCORDANCE WITH MILITARY SPECIFICATION SAE AS7928; COMMERCIAL WIRE RANGE IS 22-16
- 2
- WIRE BARREL COLOR CODED ORANGE TO DENOTE NICKEL MATERIAL
- 3
- NOTE DELETED
- 4
- GOLD PLATE 0.00127[.000050] MIN EXT THK, PER ASTM B488, TYPE1, CODE C OVER NICKEL FLASH SAE AMS QQ-N-290, OVER WOODS NICKEL FLASH PER ASTM B558.

D

C

B

A

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: SEE TABLE
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 0.26-1.65mm ² [509-3,260] CIR MILS SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	

4	260°C [500°F]	1000	LOOSE PIECE	321889-1
-	649°C [1200°F]	1000	LOOSE PIECE	2-321889-1
-		5000	ON TAPE	2-321889-3
-		1000	LOOSE PIECE	321889
FINISH	MAX OPERATING TEMPERATURE	QUANTITY	PACKAGING TYPE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN CHK DA PATTERSON APVD DE MILLER		4-15-93				TE Connectivity Ltd.					
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC — APPLICATION SPEC —		NAME TERMINAL, RING TONGUE, HIGH TEMPERATURE, STRATO-THERM™ 22-16 AWG							
		0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± 0.127[.005] 4 PLC ± — ANGLES ± —		WEIGHT		SIZE A2		CAGE CODE 00779		DRAWING NO C-321889		RESTRICTED TO —	
MATERIAL NICKEL PER ASTM B-152 ANNEALED		FINISH SEE TABLE		CUSTOMER DRAWING		SCALE 10:1		SHEET 1 OF 1		REV G4			