










WIRE RANGE :
2,1-3,3 mm²
INSULATION RANGE :
3,0-4,3mm DIA.



DO NOT SCALE
DIMENSIONS IN mm

METRIC

THIRD ANGLE
PROJECTION

NOTES:

- 1 FOR USE ON MINIATURE APPLICATORS(LEFT-RIGHT FEED)
- 2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

	1	TINPLATED	BRASS	160786-5					
	1	-	BRASS	160786-4					
	1	SILVERPLATED	Ph BRONZE	160786-3					
	1	TINPLATED	Ph BRONZE	160786-2					
	1	-	Ph BRONZE	160786-1					
PLATING		PLATING		MATERIAL		PARTNUMBER			
-	-	-	-	-	-	CUSTOMER DRAWING			
-	-	-	-	-	-	FOR REFERENCE ONLY			
-	-	-	-	-	-	WILL NOT BE UPDATED			
-	-	-	-	-	-	© COPYRIGHT 19 - BY AMP HOLLAND B.V.			
-	-	-	-	-	-	ALL INTERNATIONAL RIGHTS RESERVED.AMP PRODUCTS MAY BE			
-	-	-	-	-	-	COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.			
-	-	-	-	-	-	THIS DRAWING IS UNPUBLISHED			
-	-	-	-	-	-	RELEASED FOR PUBLICATION ,19			
C2	ECR-17-012072	DL	TD	29-08-17		AMP AMP HOLLAND B.V. 's-Hertogenbosch, The Netherlands.			
C1	ECO-09-024717	KK	AEG	05-11-09					
C	H-9671	JvL	AB	16-10-95					
LTR.	REVISION RECORD	DR.	CHK.	DATE		NAME			
						.250 SRS FASTIN-FASTON TAB			
DR.:	J.v.LIEMPT.	CHK.:	A.BIJNEN.	APP.:	M.v.DRIEL	DWG.No.		REV.LTR.	SHEET
DATE:	16 OCT 1995	DATE:	-	DATE:	-	160786		C2	1 OF 1
									A3