

FLIR E-Series bx

The New E40bx, E50bx and E60bx, Now with MSX® Advanced Thermal Imaging Camera Performance

Get more IR inspections done, create professional detailed reports easier, and share images and findings faster with FLIR's latest E-Series bx thermal imagers. Featuring a fresh array of imaging, communication, and productivity tools to help you take care of more customers.

FLIR Tools Mobile Communication – Connect an E-Series bx camera to smartphones and tablets with our Wi-Fi app. Stream live video so customers can watch along. Import radiometric JPEGs, adjust levels and color, add measurement tools, then send images off in simple reports via email to get a faster yes for repairs.

Superior Thermal Imaging – Up to 76,800 pixels (320 × 240) for better long-range accuracy and the highest level of point & shoot camera IR resolution.

MSX Thermal Image Enhancement – See structural features, numbers, and other key visual details not normally apparent in a regular thermal image with an all-in-one thermal picture that instantly orients you to right where heat issues are.

Onboard Digital Camera – 3.1MP resolution provides clear visible light reference pictures; includes built-in LED lamp that doubles as a flashlight plus a laser pointer to mark locations.

Large Touchscreen with Auto-Orientation – The E-Series touchscreen provides an intuitive interface that takes full advantage of the entire 3.5" display for easy access to diagnostics tools – now with auto-orientation to keep measurement and other data overlays upright no matter how you hold the camera.

Picture-in-Picture – Overlay thermal images onto digital scenes for extra location documentation.

Multiple Measurements – Add up to 3 box areas and 3 moveable spots using the touchscreen to gather more detailed temperature information

MeterLink® – Measure more than temperature. Send diagnostics data by Bluetooth from compatible clamp and moisture meters directly to E-Series bx cameras to embed extra information into thermal images as you capture them that further supports findings.

Interchangeable Lenses and Manual Focus – Optional wide-angle and telephoto optics let you capture more of a scene in one shot or get in closer to measure smaller, distant targets. Full focus control help you dial in the sharpest clarity and accuracy.

Greater Temperature Sensitivity – See subtler temperature patterns and detail with <0.045°C sensitivity.



FLIR Tools Mobile Wi-Fi Connectivity



Large 3.5" Touchscreen



Auto-Orientation Keeps Diagnostics Overlays Upright



Visible Light Pictures Align with Thermal Images: 3.1MP Digital Camera, LED Lamp, and Laser Pointer



Large Buttons for Easy Glove-Handed Operation









MSX Image Enhancement



Bluetooth® METERLink® Communication



Applications



Missing Insulation - Solar Cell Failure - Moisture Intrusion

Radiant Heat Tubing - Cold Draft - Air Infiltration

Imaging Specifications

FEATURES	FLIR E40bx	FLIR E50bx	FLIR E60bx
Thermal sensitivity (N.E.T.D)	<0.045°C at 30°C	<0.045°C at 30°C	<0.045°C at 30°C
Detector Type - Focal plane array; (FPA) uncooled microbolometer	160 x 120 pixels	240 x 180 pixels	320 x 240 pixels
MSX® Thermal Image Enhancement	Yes	Yes	Yes
Picture-in-Picture (P-i-P)	Fixed P-i-P	Scalable P-i-P	Scalable P-i-P
MPEG 4 Video Recording	Yes	Yes	Yes
Video Camera w/Lamp & Laser	3.1MP/LED Lamp/Laser Pointer	3.1MP/LED Lamp/Laser Pointer	3.1MP/LED Lamp/Laser Pointer
Digital Zoom	2X Continuous	4X Continuous	4X Continuous
Image modes	Thermal, Image Gallery, Visual	Thermal, Image Gallery, Visual	Thermal, Image Gallery, Visual
Image annotation	Voice (60s)/Text Comments	Voice (60s)/Text Comments	Voice (60s)/Text Comments
Moveable Spot	3 Spotmeters	3 Spotmeters	3 Spotmeters
Area Box	3 Area Boxes (full image with min/max/avg)	3 Area Boxes (full image with min/max/avg)	3 Area Boxes (full image with min/max/avg)
Delta T	Yes	Yes	Yes
Data Communication Interface	USB-mini, USB-A, Composite Video, Bluetooth, Wi-Fi	USB-mini, USB-A, Composite Video, Bluetooth, Wi-Fi	USB-mini, USB-A, Composite Video, Bluetooth, Wi-Fi
COMMON FEATURES			
Temperature range	-4 to 248°F (-20 to 120°C)		
Frame Rate	60Hz		
Field of view / Focus	25° x 19° / Manual (Minimum focus distance 1.3ft/0.4m)		
Spectral range	7.5 to 13µm		
Display	Built-in 3.5" color LCD		
Image Storage	>1000 radiometric JPEG images (SD card memory)		
Laser Classification/Type	Class 2/Semiconductor AlGaInP Diode Laser: 1mW/635nm (red)		
Set-up controls	Mode selector, color palettes, configure image info, units, language, date and time formats, and image gallery		
Measurement modes	Auto hot/cold spot, Isotherm (above/below/interval), insulation and humidity alarms		
Measurement Correction	Reflected ambient temperature & emissivity correction		
Battery Type/Operating Time	Li-Ion/ >4 hours, Display shows battery status		
Charging system	In camera AC adapter/2 bay charging system		
Shock/Vibration/Drop/Encapsulation; Safety	25G, IEC 60068-2-29/ 2G, IEC 60068-2-6/ Drop-proof 2m (6.6ft) / IP54; EN/UL/CSA/PSE 60950-1		
Dimensions/Weight	9.7x3.8x7.2" (246x97x184mm)/<1.82lbs (825g), including battery		
Dimensions/Weight	9.7x3.8x7.2" (246x97x184mm)/<1.82lbs (825g), including battery		

Ordering Information

64501-0501	FLIR E40bx Bldg. IR Camera w/MSX 160 x 120 Resolution/60Hz
64501-0501-KIT	FLIR E40bx w/MSX 160 x 120 Resolution/60Hz with FLIR Tools +
64501-0601	FLIR E50bx Bldg. IR Camera w/MSX 240 x 180 Resolution/60Hz
64501-0601-KIT	FLIR E50bx w/MSX 240 x 180 Resolution/60Hz with FLIR Tools +
64501-0702	FLIR E60bx Bldg. IR Camera w/MSX 320 x 240 Resolution/60Hz
64501-0702-KIT	FLIR E60bx w/MSX 320 x 240 Resolution/60Hz with FLIR Tools +

ACCESSORIES

T197752	Li-Ion Rechargeable Battery
T910814	AC Adapter Charger (110-240V, U.S. Plug)
T910490	Cigarette Lighter Adapter Kit, 12VDC (1.2m cable)
T198125	2-Bay Battery Charger including Power Supply (multi plugs)
T197771	Bluetooth® Headset
T197717	FLIR Reporter Professional Analysis Software
T196961	15° Telephoto Lens with Case
T196960	45° Wide Angle Lens with Case
T197926	Tripod adapter
T127100	Sunshield
T911087	Pouch
T127648	FLIR Tools+ (license only)



BOSTON

FLIR Systems, Inc.
PH: +1 866.477.3687
PH: +1 978.901.8000

PORTLAND

Corporate Headquarters
FLIR Systems, Inc.
PH: +1 866.477.3687

CANADA

FLIR Systems, Ltd.
PH: +1 800.613.0507

MEXICO/LATIN AMERICA

FLIR Systems Brasil
Av. Antonio Bardella
PH: +55 15 3238 8070



10-Year Detector
Protection
5-Year Battery
2-Year Parts & Labor

Equipment described herein may require US Government authorization for export purposes. Diversion contrary to US law is prohibited. Imagery used for illustration purposes only. Specifications are subject to change without notice. ©2013 FLIR Systems, Inc. All rights reserved. 3591 (Rev. 09/13)

www.flir.com
NASDAQ: FLIR