


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00		G1	REVISED PER ECO-11-004820	11MAR11	RK	HMR



1. 0.00076 [0.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [0.000100] MIN BRIGHT TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA OVER 0.0013 [0.000050] MIN NICKEL.
2. WIRE RANGE: 0.12 – 0.4mm² (26–22 AWG).
3. INSULATION RANGE: 1.20–1.75[0.047–0.069] DIA.
4. DIMENSIONS IN BRACKETS ARE IN INCHES.
5. 0.00076 [0.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [0.000100] MIN BRIGHT TIN IN LOCALIZED TIN PLATE AREA OVER 0.0013 [0.000050] MIN NICKEL.

5	0.20 [0.008] BRASS	1-770985-0
1	0.20 [0.008] BRASS	770985-3
PRE-TIN	0.20 [0.008] BRASS	770985-1
FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. HOOVER 05MAR03	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK C. JONES 05MAR03				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C. JONES 05MAR03	NAME			
0 PLC ± -		PRODUCT SPEC	PIN, LOOSE PIECE MINI UNIVERSAL MATE-N-LOK(TM)			
1 PLC ± -		APPLICATION SPEC				
2 PLC ± 0.13[0.005]		—	SIZE			
3 PLC ± -		—	CAGE CODE			
4 PLC ± -		—	DRAWING NO			
ANGLES ± -		—	RESTRICTED TO			
FINISH		—	A2 00779 C= 770985			
MATERIAL		—	SCALE 10:1 SHEET 1 OF 1 REV G1			
—		—	CUSTOMER DRAWING			

METRIC