





SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
ON	OFF	ON
2-3 5-6	OPEN	2-1 5-4



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. PLATING MATERIAL: SILVER
5. RATING: 2 AMPS @250VAC
5 AMPS @120VAC or 28VDC
6. ELECTRIC LIFE: 40,000 make-and-break cycles at full load.
7. INSULATION RESISTANCE: 1,000 Mega-ohm min.
8. DIELECTRIC STRENGTH: 1,000 V RMS @sea level.
9. OPERATING TEMP.: -30°C to 85°C
10. ▲ DENOTES CRITICAL PARAMETER.
11. PACKAGE: 108 PARTS PER TRAY
12. 2011/65/EU (ROHS) COMPLIANT
13. HARDWARE TO BE SHIPPED BULK:
T100000 HEXNUT - QTY 2
T100011 LOCKWASHER - QTY 1
T100015 LOCKRING - QTY 1



E-SWITCH®

B	22780	update print	3/28/17	MW
A	17965	RELEASE FOR PRODUCTION	2/13/08	BLR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE 100DP3T2B3M2QEH

SCALE
2:1DATE
2/13/2008DR
BLRDWG
ST123017REV
B